



This document is the property of Xinshengyue Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Xinshengyue Corporation without its prior consent&that no right is granted to disclose or to use any information in this document.

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A	ECN NO.	INITIAL RELEASED	2026.09.01	JASON



**RoHS
Compliant**



SPECIFICATIONS:

Current Rating:3.0 Amps
Withstanding Voltage: AC 1000V
Insulation Resistance:1000MΩ Min
Contact Resistance: 20mΩ Max
Operation Temperature:-40 °C to+105 °C
Insulator Material:Polyester(UL94V-0) PBT
Contact Material:Brass
Contact Plating:Gold Flash
Max.Processing Temp: 200 °C for30-60seconds
220 °C for 5seconds)

RECOMMEND P.C.B LAYOUT
TOLERANCE:±0.05(TOP VIEW)



P/N: 105103-241XX1

05:PIN
HEADER

1:PITCH 2.54

SERIES NUMBER
XX: 01~99

—SERIES NO.1,2,3...

- PER ROW PIN NUMBER

XX: 01~99

- CONTACT PLATED

1: G/F Au

- PACKAGING:4:BAG

— ROW:2:DOUBLE

Dimension Table:

No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
1	0.00	2.54	11	25.40	27.94	21	50.80	53.34	31	76.20	78.74
2	2.54	5.08	12	27.94	30.48	22	53.34	55.88	32	78.74	81.28
3	5.08	7.62	13	30.48	33.02	23	55.88	58.42	33	81.28	83.82
4	7.62	10.16	14	33.02	35.56	24	58.42	60.96	34	83.82	86.36
5	10.16	12.70	15	35.56	38.10	25	60.96	63.50	35	86.36	88.90
6	12.70	15.24	16	38.10	40.64	26	63.50	66.04	36	88.90	91.44
7	15.24	17.78	17	40.64	43.18	27	66.04	68.58	37	91.44	93.98
8	17.78	20.32	18	43.18	45.72	28	68.58	71.12	38	93.98	96.52
9	20.32	22.86	19	45.72	48.26	29	71.12	73.66	39	96.52	99.06
10	22.86	25.40	20	48.26	50.80	30	73.66	76.20	40	99.06	101.60

TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING	XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD.			
X.X ±0.30	X.* ±10°	PART NO. SEE P/N	TITLE: 2.54 PIN HEADER H2.5 DOUBLE ROW VERTICAL DIP L11.5			
.XX ±0.20	.X* ± 8°		DRAWG NO. C-105103-2			
.XXX ±0.10	.XX* ± 5°					
UNIT	mm	DESIGN: JASON		SCALE 1:1	SHEET 1/1	REV. A
MATERIAL	---	CHED: JASON				
FINISH	---	APPD: ARAY				