

Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
100V	15mΩ@10V	40A
	18mΩ@4.5V	



合肥矽普半导体

Siliup Semiconductor Technology Co., Ltd

技术 品质 服务

www.siliup.com


Feature

- Fast Switching
- Low Gate Charge and Rdson
- Advanced Split Gate Trench Technology
- 100% Single Pulse avalanche energy Test


Applications

- Power switching application
- Battery management
- Uninterruptible power supply


Package



Circuit diagram



Marking



SP010N15GTH : Product code
****** : Week code

Order Information

Device	Package	Unit/Tube
SP010N15GTH	TO-252	2500

Absolute maximum ratings (Ta=25°C unless otherwise noted)

Parameter	Symbol	Rating	Unit
Drain-Source Voltage	V_{DS}	100	V
Gate-Source Voltage	V_{GS}	± 20	V
Continuous Drain Current (Tc=25°C)	I_D	40	A
Continuous Drain Current (Tc=100°C)	I_D	27	A
Pulsed Drain Current	I_{DM}	160	A
Single Pulse Avalanche Energy ¹	E_{AS}	132	mJ
Power Dissipation (Tc=25°C)	P_D	65	W
Power Dissipation (Tc=100°C)	P_D	26	W
Thermal Resistance Junction-to-Case	$R_{\theta JC}$	1.92	°C/W
Storage Temperature Range	T_{STG}	-55 to 150	°C
Operating Junction Temperature Range	T_J	-55 to 150	°C


Electrical characteristics (Ta=25°C, unless otherwise noted)

Characteristics	Symbol	Test Condition	Min	Typ	Max	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	VGS=0V , ID=250uA	100	-	-	V
Drain Cut-Off Current	IDSS	VDS=80V , VGS=0V , TJ=25℃	-	-	1	μA
Gate Leakage Current	IGSS	VGS=±20V , VDS=0V	-	-	±100	nA
Gate Threshold Voltage	VGS(th)	VGS=VDS , ID=250uA	1.5	1.9	2.5	V
Drain-Source ON Resistance	RDS(ON)	VGS=10V , ID=20A	-	15	19	mΩ
		VGS=4.5V , ID=10A	-	18	24	
Gate Resistance	RG	VDS=50V , VGS=0V , f=1MHz	-	2.16	-	Ω
Dynamic Characteristics						
Input Capacitance	Ciss	VDS=50V , VGS=0V , f=1MHz	-	925	-	pF
Output Capacitance	Coss		-	258	-	
Reverse Transfer Capacitance	Crss		-	14	-	
Total Gate Charge	Qg	VDS=50V , VGS=10V , ID=20A	-	16	-	nC
Gate-Source Charge	Qgs		-	5	-	
Gate-Drain Charge	Qgd		-	2.7	-	
Gate Plateau Voltage	Vplateau		-	3.6	-	V
Switching Characteristics						
Turn-On Delay Time	td(on)	VDD=50V, VGS=10V , RG=2.2Ω , ID=20A	-	38	-	nS
Rise Time	tr		-	12	-	
Turn-Off Delay Time	td(off)		-	51	-	
Fall Time	tf		-	17	-	
Drain-Source Body Diode Characteristics						
Source-Drain Diode Forward Voltage	VSD	IS=1A , VGS=0V , TJ=25℃	-	-	1.2	V
Maximum Body-Diode Continuous Current	IS		-	-	40	A
Reverse Recovery Time	Trr	IS=20A , di/dt=100A/us , TJ=25℃	-	40	-	nS
Reverse Recovery Charge	Qrr		-	42	-	nC


Note:

- The EAS test condition is $V_{DD}=50V, V_{GS}=10V, L=0.5mH, R_G=25\Omega$


Typical Characteristics




Typical Output Characteristics




Transfer Characteristics




On-Resistance vs. Drain Current








On-Resistance vs. Junction Temperature



Gate Charge





Capacitance Characteristics





Test Circuit



Gate Charge





Resistive Load Switching Time



Un-clamped Inductive Load Switching




Drain-Source Body Diode Reverse Recovery





Temperature Profile for IR Reflow Soldering



Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Preheat & Soak		
Temperature min (T_{Smin})	100°C	150°C
Temperature max (T_{Smax})	150°C	200°C
Time (T_{Smin} to T_{Smax}) (t_s)	60-120 seconds	60-120 seconds
Average ramp-up rate (T_{Smax} to T_P)	3 °C/second max.	3°C/second max.
Liquidous temperature (T_L)	183 °C	217°C
Time at liquidous (t_L)	60-150 seconds	60-150 seconds
Peak package body Temperature e (T_P)*	See Classification Temp in table 1	See Classification Temp in table 2
Time (t_P)** within 5°C of the specified classification temperature (T_C)	20** seconds	30** seconds
Average ramp-down rate (T_P to T_{Smax})	6 °C/second max.	6 °C/second max.
Time 25°C to peak temperature	6 minutes max.	8 minutes max.
* Tolerance for peak profile Temperature (T_P) is defined as a supplier minimum and a user maximum. ** Tolerance for time at peak profile temperature (t_P) is defined as a supplier minimum and a user maximum		


Table 1. SnPb Eutectic Process – Classification Temperatures (T_C)

Package Thickness	Volume mm ³ <350	Volume mm ³ ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2. Pb-free Process – Classification Temperatures (T_C)

Package Thickness	Volume mm ³ <350	Volume mm ³ 350-2000	Volume mm ³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 mm – 2.5 mm	260 °C	250 °C	245 °C
≥2.5 mm	250 °C	245 °C	245 °C

TO-252 Embossed Carrier Tape




Packaging Description:


TO-252 parts are shipped in tape. The carrier tape is made from a dissipative (carbon filled) polycarbonate resin. The cover tape is a multilayer film (Hear Activated Adhesive in nature) primarily composed of polyester film, adhesive layer, sealant, and anti-static sprayed agent. These reeled parts in standard option are shipped with 2500 units per 13" or 33.0 cm diameter reel. The reels are clear in color and is made of polystyrene plastic (anti-static coated).

Dimensions are in millimeter										
Pkg type	A	B	C	d	E	F	P0	P	P1	W
TO-252	6.90	10.50	2.70	Φ1.55	1.75	7.50	4.00	8.00	2.00	16.00

TO-252 Tape Leader and Trailer




TO-252 Reel



Dimensions are in millimeter						
Reel	D	D1	D2	W1	W2	I
13" Dia	330.00	100.00	Φ21.00	16.40	21.40	Φ13.00

Reel	Reel Size	Box	Box Size(mm)	Carton	Carton Size(mm)
2500 pcs	13 inch	5000 pcs	360×360×65	25000 pcs	378×358×382

TO-252 Package Information


Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	2.200	2.400	0.087	0.094
A1	0.000	0.127	0.000	0.005
b	0.660	0.860	0.026	0.034
c	0.460	0.580	0.018	0.023
D	6.500	6.700	0.256	0.264
D1	5.100	5.460	0.201	0.215
D2	4.830 REF.		0.190 REF.	
E	6.000	6.200	0.236	0.244
e	2.186	2.386	0.086	0.094
L	9.800	10.400	0.386	0.409
L1	2.900 REF.		0.114 REF.	
L2	1.400	1.700	0.055	0.067
L3	1.600 REF.		0.063 REF.	
L4	0.600	1.000	0.024	0.039
ϕ	1.100	1.300	0.043	0.051
θ	0°	8°	0°	8°
h	0.000	0.300	0.000	0.012
V	5.350 REF.		0.211 REF.	