

E

RoHS Compliant

E

B+0.4±0.3

A±0.1

2.5±0.15

2.54

ø1.02

A

RECOMMEND P.C.B LAYOUT
TOLERANCE:±0.05(TOP VIEW)

8.5±0.15

2.54±0.1

PIN 0.64*0.4

3.0±0.2

P/N: 104101-141XX1

04:FEMALE
HEADER

1:PITCH 2.54

SERIES NO.1,2,3...

PER ROW PIN NUMBER

XX: 01~99

CONTACT PLATED

1: G/F Au

PACKAGING:4:BAG

1:ROW SINGLE

SERIES NUMBER

XX: 01~99

Dimension Table:

No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
1	0.00	2.54	11	25.40	27.94	21	50.80	53.34	31	76.20	78.74
2	2.54	5.08	12	27.94	30.48	22	53.34	55.88	32	78.74	81.28
3	5.08	7.62	13	30.48	33.02	23	55.88	58.42	33	81.28	83.82
4	7.62	10.16	14	33.02	35.56	24	58.42	60.96	34	83.82	86.36
5	10.16	12.70	15	35.56	38.10	25	60.96	63.50	35	86.36	88.90
6	12.70	15.24	16	38.10	40.64	26	63.50	66.04	36	88.90	91.44
7	15.24	17.78	17	40.64	43.18	27	66.04	68.58	37	91.44	93.98
8	17.78	20.32	18	43.18	45.72	28	68.58	71.12	38	93.98	96.52
9	20.32	22.86	19	45.72	48.26	29	71.12	73.66	39	96.52	99.06
10	22.86	25.40	20	48.26	50.80	30	73.66	76.20	40	99.06	101.60

TOLERANCE	NAME(INTENDED USE) CUSTOMER DRAWING	XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD			
X.X ±0.30	X.* ±10*	PART NO. SEE P/N	TITLE: 2.54 FEMALE HEADER H8.5 SINGLE DIP		
.XX ±0.20	.X* ± 8*		DRAWG NO. C-104101-1		
.XXX ±0.10	.XX* ± 5*				
UNIT	mm	DESIGN: JASON		SCALE	SHEET
MATERIAL	---	CHED: JASON		1:1	1/1
FINISH	---	APPD: ARAY		REV.	A