

Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
40V	2.7m Ω @10V	90A
	4.0m Ω @4.5V	



合肥矽普半导体

Siliup Semiconductor Technology Co., Ltd

技术 品质 服务

www.siliup.com


Feature

- Fast switching speed
- Low Gate Charge and Rdson
- Advanced Split Gate Trench Technology
- 100% Single Pulse avalanche energy Test

Applications


- DC-DC Converters
- Motor Control
- Portable equipment application

Package



PDFN5X6-8L

Circuit diagram



Marking



SP40N03GNK : Device Code
** : Week Code

Order Information

Device	Package	Unit/Tape
SP40N03GNK	PDFN5X6-8L	5000

Absolute maximum ratings (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Rating	Unit
Drain-Source Voltage	V_{DSS}	40	V
Gate-Source Voltage	V_{GSS}	± 20	V
Continuous Drain Current (Tc=25°C)	I_D	90	A
Continuous Drain Current (Tc=100°C)	I_D	60	A
Pulse Drain Current Tested	I_{DM}	360	A
Single pulsed avalanche energy ¹	E_{AS}	169	mJ
Power Dissipation (Tc=25°C)	P_D	65	W
Power Dissipation (Tc=100°C)	P_D	26	W
Thermal Resistance Junction-to-Case	$R_{\theta JC}$	1.92	°C/W
Storage Temperature Range	T_{STG}	-55 to 150	°C
Operating Junction Temperature Range	T_J	-55 to 150	°C


Electrical characteristics (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	VGS=0V , ID=250uA	40	-	-	V
Drain-Source Leakage Current	IDSS	VDS=32V , VGS=0V , TJ=25℃	-	-	1	uA
Gate-Source Leakage Current	IGSS	VGS=±20V , VDS=0V	-	-	±100	nA
Gate Threshold Voltage	VGS(th)	VGS=VDS , ID =250uA	1.1	1.5	2.1	V
Static Drain-Source On-Resistance	RDS(ON)	VGS =10V, ID =20A	-	2.7	3.3	mΩ
		VGS =4.5V, ID =10A	-	4.0	5.3	
Gate Resistance	RG	VDS=20V , VGS=0V , f=1MHz		1.2		Ω
Dynamic characteristics						
Input Capacitance	Ciss	VDS=20V , VGS=0V , f=1MHz	-	2398	-	pF
Output Capacitance	Coss		-	441	-	
Reverse Transfer Capacitance	Crss		-	17	-	
Total Gate Charge	Qg	VDS=20V , VGS=20V , ID=30A	-	37	-	nC
Gate-Source Charge	Qgs		-	11.5	-	
Gate-Drain Charge	Qgd		-	8	-	
Gate Plateau Vlotage	Vplateau		-	3.65	-	V
Switching Characteristics						
Turn-On Delay Time	Td(on)	VDD=20 VGS=20V , RG=3Ω, ID=30A	-	11.5	-	nS
Rise Time	Tr		-	8	-	
Turn-Off Delay Time	Td(off)		-	46	-	
Fall Time	Tf		-	9	-	
Diode Characteristics						
Diode Forward Voltage	VSD	VGS=0V , IS=1A , TJ=25℃	-	-	1.2	V
Diode Continuous Current	IS		-	-	90	A
Reverse recover time	Trr	IS=20A, di/dt=100A/us, Tj=25℃	-	14	-	nS
Reverse recovery charge	Qrr		-	23	-	nC


Note:

- The EAS Test condition is $V_{DD}=20V, V_{GS}=10V, L=0.5mH, R_G=25\Omega$


Typical Characteristics




Output Characteristics




Transfer Characteristics




Capacitance Characteristics




Gate Charge




Current dissipation




Power dissipation




$R_{DS(on)}$ VS Drain Current




Forward characteristics of reverse diode




Normalized breakdown voltage



Normalized Threshold voltage





Maximum Transient Thermal Impedance





Safe Operation Area

Test Circuit



Gate Charge





Resistive Load Switching Time




Un-clamped Inductive Load Switching



Drain-Source Body Diode Reverse Recovery



Temperature Profile for IR Reflow Soldering



Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Preheat & Soak		
Temperature min (T_{Smin})	100°C	150°C
Temperature max (T_{Smax})	150°C	200°C
Time (T_{Smin} to T_{Smax}) (t_s)	60-120 seconds	60-120 seconds
Average ramp-up rate (T_{Smax} to T_P)	3 °C/second max.	3°C/second max.
Liquidous temperature (T_L)	183 °C	217°C
Time at liquidous (t_L)	60-150 seconds	60-150 seconds
Peak package body Temperature e (T_P)*	See Classification Temp in table 1	See Classification Temp in table 2
Time (t_P)** within 5°C of the specified classification temperature (T_C)	20** seconds	30** seconds
Average ramp-down rate (T_P to T_{Smax})	6 °C/second max.	6 °C/second max.
Time 25°C to peak temperature	6 minutes max.	8 minutes max.
* Tolerance for peak profile Temperature (T_P) is defined as a supplier minimum and a user maximum. ** Tolerance for time at peak profile temperature (t_P) is defined as a supplier minimum and a user maximum		


Table 1. SnPb Eutectic Process – Classification Temperatures (T_C)

Package Thickness	Volume mm ³ <350	Volume mm ³ ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2. Pb-free Process – Classification Temperatures (T_C)

Package Thickness	Volume mm ³ <350	Volume mm ³ 350-2000	Volume mm ³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 mm – 2.5 mm	260 °C	250 °C	245 °C
≥2.5 mm	250 °C	245 °C	245 °C


PDFN5X6-8L Embossed Carrier Tape




Dimensions are in millimeter

Pkg type	A	B	C	d	E	F	P0	P	P1	W
PDFN5X6-8L	6.30	5.30	1.10	Φ1.50	1.75	5.50	4.00	8.00	2.00	12.00

PDFN5X6-8L Tape Leader and Trailer



PDFN5X6-8L Reel




Dimensions are in millimeter


Reel Option	D	D1	D2	G	W1	W2
13"Dia	Ø330.00	100.00	13.00	1.90	17.60	12.40

REEL	Reel Size	Box	Box Size(mm)	Carton	Carton Size(mm)
5,000 pcs	13 inch	5,000 pcs	340×336×29	50,000 pcs	353×346×365


PDFN5X6-8L Package Information



Top View
[顶视图]



Bottom View
[背视图]



Side View
[侧视图]

Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	0.900	1.120	0.035	0.044
b	0.330	0.510	0.013	0.020
C	0.110	0.340	0.004	0.013
D	4.700	5.260	0.185	0.207
D1	4.700	5.100	0.185	0.201
D2	3.560	4.500	0.140	0.177
E	5.750	6.250	0.226	0.246
E1	5.600	6.000	0.220	0.236
E2	3.180	3.660	0.125	0.144
e	1.170	1.370	0.046	0.054
L	0.350	0.710	0.014	0.028
L1	0.060	0.200	0.002	0.008
H	0.350	0.710	0.014	0.028