

Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
30V	6mΩ@10V	35A
	7.5mΩ@4.5V	



合肥矽普半导体

Siliup Semiconductor Technology Co., Ltd

技术 品质 服务

www.siliup.com


Feature

- Fast Switching
- Low Gate Charge and Rdson
- Advanced Split Gate Trench Technology
- **100% UIS TESTED**

Applications


- Power switching application
- DC-DC Converters

Package




PDFN5X6-8L

Circuit diagram



Marking



30N06G
*

:Device Code
:Month Code

Order Information

Device	Package	Unit/Tape
SP30N06GNK	PDFN5X6-8L	5000

Absolute maximum ratings (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Rating	Units
Drain-Source Voltage	V_{DS}	30	V
Gate-Source Voltage	V_{GS}	± 20	V
Continuous Drain Current (Tc=25°C)	I_D	35	A
Continuous Drain Current (Tc=100°C)	I_D	23.3	A
Pulsed Drain Current	I_{DM}	140	A
Single Pulse Avalanche Energy ¹	E_{AS}	39.2	mJ
Power Dissipation (Tc=25°C)	P_D	28	W
Power Dissipation (Tc=100°C)	P_D	11.2	W
Thermal Resistance Junction-to-Case	$R_{\theta JC}$	4.5	°C/W
Storage Temperature Range	T_{STG}	-55 to 150	°C
Operating Junction Temperature Range	T_J	-55 to 150	°C


Electrical characteristics (Ta=25°C, unless otherwise noted)

Characteristics	Symbol	Test Condition	Min	Typ	Max	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	VGS=0V , ID=250uA	30	-	-	V
Drain Cut-Off Current	IDSS	VDS=30V , VGS=0V	-	-	1	uA
Gate Leakage Current	IGSS	VGS=±20V , VDS=0V	-	-	±100	nA
Gate Threshold Voltage	VGS(th)	VGS=VDS , ID =250uA	1.3	1.7	2.3	V
Drain-Source ON Resistance	RDS(ON)	VGS=10V , ID=12A	-	6.0	8.0	mΩ
		VGS=4.5V , ID=12A	-	7.5	10.0	
Gate Resistance	RG	f=1MHz	-	1.5	-	Ω
Dynamic Characteristics						
Input Capacitance	Ciss	VDS=15V , VGS=0V , f=1MHZ	-	625	-	pF
Output Capacitance	Coss		-	240	-	
Reverse Transfer Capacitance	Crss		-	25	-	
Total Gate Charge	Qg	VGS=10V , VDS=15V , ID=12A	-	10	-	nC
Gate-Source Charge	Qgs		-	3	-	
Gate-Drain Charge	Qgd		-	2	-	
Gate Plateau Voltage	Vplateau		-	3.4	-	V
Switching Characteristics						
Turn-On Delay Time	td(on)	VGS=10V , VDD=15V , ID=12A , RG=2Ω	-	7	-	nS
Rise Time	tr		-	18.8	-	
Turn-Off Delay Time	td(off)		-	19.5	-	
Fall Time	tf		-	3.4	-	
Drain-Source Body Diode Characteristics						
Source-Drain Diode Forward Voltage	VSD	IS=1A , VGS=0V	-	-	1.2	V
Maximum Body-Diode Continuous Current	IS		-	-	35	A
Reverse Recovery Time	Trr	IS=20A , di/dt=100A/us , TJ=25℃	-	11	-	nS
Reverse Recovery Charge	Qrr		-	18	-	nC


Note :

1. The test condition is $V_{DD}=15V, V_{GS}=10V, L=0.1mH, R_G=25\Omega$;


Typical Characteristics




Output Characteristics




Transfer Characteristics




Capacitance Characteristics




Gate Charge




Current dissipation




Power dissipation




RDS(on) vs. Drain Current




Forward characteristics of reverse diode




Normalized breakdown voltage



Normalized Threshold voltage





Safe Operation Area





Test Circuit



Gate Charge





Resistive Load Switching Time




Un-clamped Inductive Load Switching



Drain-Source Body Diode Reverse Recovery



Temperature Profile for IR Reflow Soldering



Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Preheat & Soak		
Temperature min (T_{Smin})	100°C	150°C
Temperature max (T_{Smax})	150°C	200°C
Time (T_{Smin} to T_{Smax}) (t_s)	60-120 seconds	60-120 seconds
Average ramp-up rate (T_{Smax} to T_P)	3 °C/second max.	3°C/second max.
Liquidous temperature (T_L)	183 °C	217°C
Time at liquidous (t_L)	60-150 seconds	60-150 seconds
Peak package body Temperature e (T_P)*	See Classification Temp in table 1	See Classification Temp in table 2
Time (t_P)** within 5°C of the specified classification temperature (T_C)	20** seconds	30** seconds
Average ramp-down rate (T_P to T_{Smax})	6 °C/second max.	6 °C/second max.
Time 25°C to peak temperature	6 minutes max.	8 minutes max.
* Tolerance for peak profile Temperature (T_P) is defined as a supplier minimum and a user maximum. ** Tolerance for time at peak profile temperature (t_P) is defined as a supplier minimum and a user maximum		


Table 1. SnPb Eutectic Process – Classification Temperatures (T_C)

Package Thickness	Volume mm ³ <350	Volume mm ³ ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2. Pb-free Process – Classification Temperatures (T_C)

Package Thickness	Volume mm ³ <350	Volume mm ³ 350-2000	Volume mm ³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 mm – 2.5 mm	260 °C	250 °C	245 °C
≥2.5 mm	250 °C	245 °C	245 °C


PDFN5X6-8L Embossed Carrier Tape




Dimensions are in millimeter

Pkg type	A	B	C	d	E	F	P0	P	P1	W
PDFN5X6-8L	6.30	5.30	1.10	Φ1.50	1.75	5.50	4.00	8.00	2.00	12.00

PDFN5X6-8L Tape Leader and Trailer



PDFN5X6-8L Reel




Dimensions are in millimeter


Reel Option	D	D1	D2	G	W1	W2
13" Dia	Ø330.00	100.00	13.00	1.90	17.60	12.40

REEL	Reel Size	Box	Box Size(mm)	Carton	Carton Size(mm)
5,000 pcs	13 inch	5,000 pcs	340×336×29	50,000 pcs	353×346×365


PDFN5X6-8L Package Information



Top View
[顶视图]



Bottom View
[背视图]



Side View
[侧视图]

Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	0.900	1.200	0.035	0.047
b	0.330	0.510	0.013	0.020
C	0.110	0.340	0.004	0.013
D	4.700	5.260	0.185	0.207
D1	4.700	5.100	0.185	0.201
D2	3.560	4.500	0.140	0.177
E	5.750	6.250	0.226	0.246
E1	5.600	6.000	0.220	0.236
E2	3.180	3.660	0.125	0.144
e	1.170	1.370	0.046	0.054
L	0.350	0.750	0.014	0.030
L1	0.000	0.200	0.000	0.008
H	0.350	0.710	0.014	0.028