






Assembly Layout



Board Layout
General Tolerance:±0.05

Specifications:

规格:

Voltage rating:150V AC/DC

额定电压: 150V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range:-25℃~+105℃

温度范围: -25℃~+105℃

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

X3000	F	R	S	- 03	- LP	SW
①	②	③	④	⑤	⑥	⑦

- 1.Series No
- 2.Category:F-Female
- 3.Welding Board Angle:R-Stright 90°
- 4.Welding Way:S-SMT
- 5.Row No.Pin No:XX-03 Pin
- 6.Material:LP-LCP UL94V-0(Beige)
- 7.Plating:SW-Matte Tin Plating

X3000FRS-03-LPSW	LCP	Phosphor Bronze	X3000W
PART NO	Material	Material(Pin)	Suitable XKB Wafer

DSND	SCALE: N/A	MODEL TYPE: 3.0mm Crimp Style Connector
DWN	VIEW:	PART NO.: X3000FRS-03-LPSW
CHKD	UNIT: mm/in	DWG NO.: X-X3000FRS-03-LPSW
APPD	SIZE: A4	WEIGHT
		SHEET
		REVISION
		1/1
		A0

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						



XKB INDUSTRIAL PRECISION CO.,LIMITED