V_{RRM}	650	V
I_F	8	A
Q_c	33	nC

Features

- Zero Forward Recovery Voltage
- Zero Reverse Recovery Current
- Excellent Surge Current Capability
- Temperature Independent Switching
- Positive Temperature Coefficient on V_F
- High Frequency Operation


Benefits

- Replace Bipolar with Unipolar Rectifiers
- Essentially No Switching Losses
- High Efficiency
- Reduction of Heat Sink Requirements
- Parallel Devices Without Thermal Runaway

Applications

- Parallel Devices Without Thermal Runaway
- Power Factor Correction
- DC-AC Inverters
- DC-DC Inverters






TO-252



Equivalent Circuit



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Maximum ratings (T_j=25℃ unless otherwise specified)

Parameter	Symbol	Test Condition	Value	Unit
Repetitive Peak Reverse Voltage	V_{RRM}		650	V
Forward Current	I_F	T_C=25℃ T_C=157℃	30 8	A
Non-Repetitive Forward Surge Current	I_{FSM}	T_C=25℃, t_p=10ms, Half Sine Wave	60	A
Power Dissipation	P_{tot}	T_C=25℃, T_j=175℃	83	W
Operating and Storage Temperature	T_j, T_{stg}		-55 to +175	℃

ELECTRICAL CHARACTERISTICS (T_C=25°C, unless otherwise specified)

Parameter	Symbol	Test Condition	Value			Unit
			Min.	Typ.	Max.	
DC Blocking Voltage	V_{DC}	T_j=25℃, I_D=500μA	650			V
Forward Voltage	V_F	I_F=8A, T_j=25℃		1.25	1.56	V
		I_F=8A, T_j=175℃		1.31		V
Reverse Current	I_R	V_R=650V, T_j=25℃			50	μA
		V_R=650V, T_j=175℃			200	μA
Total Capacitive Charge	Q_C	V_R=650V, T_j=25℃		33		nC
Total Capacitance	C	T_j=25℃ V_R=1V, f=100KHz V_R=650V, f=100KHz		 405 33		pF

Thermal Characteristics

Parameter	Symbol	Value			Unit
		Min.	Typ.	Max.	
Thermal Resistance from Junction to Case	$R_{th(j-c)}$	-	1.8	-	℃/W

RATING AND CHARACTERISTIC CURVES




Fig1. Forward Characteristics




Fig2. Reverse Characteristics




Fig3. Capacitance vs. Reverse Voltage





Fig4. Recovery Charge vs. Reverse Voltage

Soldering parameters


Reflow Condition		Pb-Free assembly (see as bellow)
Pre Heat	-Temperature Min ($T_{s(min)}$)	+150℃
	-Temperature Max($T_{s(max)}$)	+200℃
	-Time (Min to Max) (ts)	60-180 secs.
Average ramp up rate (Liquid us Temp (T_L) to peak)		3℃/sec. Max
$T_{s(max)}$ to T_L - Ramp-up Rate		3℃/sec. Max
Reflow	-Temperature(T_L)(Liquid us)	+217℃
	-Temperature(t_L)	60-150 secs.
Peak Temp (T_p)		+260(+0/-5)℃
Time within 5℃ of actual Peak Temp (t_p)		30 secs. Max
Ramp-down Rate		6℃/sec. Max
Time 25℃ to Peak Temp (T_P)		8 min. Max
Do not exceed		+260℃

FIG5: Reflow condition




Package Dimensions & Suggested Pad Layout

TO-252




Dimensions in inches and (millimeters)



Dimensions	Value (in mm)
C	4.55
X	1.50
X1	5.80
Y	2.70
Y1	6.00
Y2	10.90


Tape & rell specification

Tape



Symbol	Dimension (mm)
P0	4.00±0.20
P1	8.00±0.20
P2	2.00±0.20
D0	1.55±0.15
D1	1.55±0.20
E	1.75±0.20
F	7.50±0.20
W	16.00±0.20
A0	7.10±0.20
B0	10.50±0.20
K0	2.70±0.20
T	0.30±0.10

13” Reel



D2	330.0±5.0
D3	100.0±4.0
W1	20.0±5.0
W2	25.0±5.0
I	13.0±2.0

Quantity: 2500PCS