

1

2

3

4

A

B

C

D



A

B

C

D

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图框升级整理图面	2024.08.06	阿 树




■SPECIFICATIONS

- Voltage rating:600V AC/DC
- Current rating:9A AC/DC
- Withstanding Voltage:1500V AC/minute
- Temperature range:-45°C+125°C
- Insulation resistance:≥1000MΩ
- Contact resistance:≤10mΩ
- After environmental testing:≤20mΩ

PART NO.:

X9357 W V-2x02 FS-NO SN XX
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series No
- ② Category:W-Wafer
- ③ Welding Board Angle:V-Straight 180°
- ④ Welding Way:S-SMT
- ⑤ Row No-Pin No: 2xXX-2x01P~2x12P
- ⑥ Plug the Pin&Specal NO.:FS-The hollow needle with positioning column
- ⑦ Material:NO-PA66 94V-0;
- ⑧ Planting Category:SN-Bright tin plating
- ⑨ Color:Blank-natural color



Recommended P.C.B Layout
General Tolerance±0.05

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2x01	—	5.60	2x07	25.20	30.80
2x02	4.20	9.80	2x08	29.40	35.00
2x03	8.40	14.00	2x09	33.60	39.20
2x04	12.60	18.20	2x10	37.80	43.40
2x05	16.80	22.40	2x11	42.00	47.60
2x06	21.00	26.60	2x12	46.20	51.80

X9357WV-2x02FS-N0SN	Nylon 66 UL 94V-2	Brass	Tin-Plated	X9357H
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	阿 树	VIEW:				MODEL TYPE:	4.20 mm Crimp Style Connector		
CHECKED		UNIT: mm/in				PART NO.:	X9357WV-2x02FS-N0SN		
APPROVED		SIZE: A4				DWG NO.:	X-X9357WV-2x02FS-N0SN		
PRECISION CO.,LIMITED						SCALE	PAGE	REVISION	
						N/A	1/1	A1	

1

2

3

4