






平推钮 (R)



电路图



高推钮 (E)



PCB开孔

位数	尺寸A (mm)
02	6.64
03	9.18
04	11.72
05	14.26
06	16.80
07	19.34
08	21.88
09	24.42
10	26.96
12	32.04

开关特性:

- 1、开关容量: 切换时:25mA @24VDC
非切换时:100mA @50VDC
- 2、绝缘电阻: 100MΩ at 500VDC
- 3、接触电阻: 初始值50mΩ max 寿命终值100mΩ max
- 4、绝缘强度: 500VAC 50Hz /1min
- 5、极间电容: <5pf, 1MHz±10kHz
- 6、操作力: 500gf max
- 7、电气寿命: 2000次 <100mΩ@ 20次/min, 25mA 24VDC
- 8、适用温度: -20℃ to 85℃ (无结冰)
- 9、焊接要求:
手工焊接: 320° C不超过2秒. (30瓦烙铁max.)
波峰焊: 260℃不超过5秒, 在焊接和清洁过程中开关处于断开状态
- 10、开关出厂处于断开状态。

材料:

盖子:PBT塑料(红色或蓝色或黑色)
底座:PBT塑料(黑色)
操作杆:PBT塑料(白色)
灌封胶: 环氧树脂
端子: 磷铜,
电镀:
全金: 接触点镀镍底40μ", 镀金1.5μ"
插针脚镀镍底20μ", 镀金0.5μ"
半锡金: 接触点镀镍底40μ", 镀金1.5μ"
插针脚镀镍底20μ", 镀镀锡50μ"

						 深圳市首韩科技有限公司				
						外观图			拨码开关	
标记	处数	分区	更改文件号	签名	年月日	阶段标记		重量		比例
设计	李春风		标准化							2.54-2P WJCJ-BL
								1	4:1	
审核	钟华华									
工艺			批准	罗孝金		共 张 第 张				



深圳市首韩科技有限公司

SHENZHEN SHOUHAN TECHNOLOGY CO., LTD

Tel: 0755-27597601 Fax: 0755-27597491

承 认 书

SPECIFICATION FOR APPROVAL

产 品 编 码
material code:

产品名称 Project:

拨码开关

规格型号 Part No:

2.54-2P WJCJ-BL

贵公司承认印 Approval signatures

料 号/Part No.	签 章/Signatures

日期 Date:

拟制/Drawn	李春风	
审核/Check	钟华华	
批准/Approved	罗孝金	



规格书

DIPSWITCH DATASHEET

1. 通则 Rule:

1.1: 测试条件：标准测试除非特别规定必须在温度5-35℃,相对湿度45-85%及860-1060 HPa大气压力下进行。如上述条件仍有问题发生,需在重新再次测试时,其测试条件须限定在温度 $20 \pm 2^\circ\text{C}$,相对湿度 $65 \pm 5\%$ 及860-1060 HPa大气压力。

1.1: Test conditions: Unless otherwise specified, standard tests must be conducted at temperatures of 5-35℃, relative humidity of 45-85%, and atmospheric pressure of 860-1060 HPa. If there are still issues with the above conditions, the testing conditions must be limited to a temperature of $20 \pm 2^\circ\text{C}$, a relative humidity of $65 \pm 5\%$, and an atmospheric pressure of 860-1060 HPa when retesting.

12: 工作温度范围: -30~85℃ 贮存温度范围: -40~85℃

1.2: Working temperature range: -30~85℃ Storage temperature range: -40~85℃

2. 额定功率: 开关在 ON 状况时, DC24V, 25mA。

3. 电气性能 Electrical performance:

item	Name	Test conditions	Spec
3.1	接触阻抗 Contact impedance	AC 1KHz $\pm$ 200Hz 电压20mv以下电流50mA 以下, 或者DC5V 10mA AC 1KHz $\pm$ 200Hz voltage below 20mV current below 50mA, or DC5V 10mA	Max 100m Ω
3.2	绝缘阻抗 Insulation impedance	电压DC500V, 60 $\pm$ 5秒, 相邻两个端子 Voltage DC500V, 60 $\pm$ 5 seconds, adjacent to two terminals	Min 100M Ω
3.3	耐电压 withstanding voltage	60 $\pm$ 5秒相邻两个端子间测定 电压AC500V(50~60Hz, 电流2mA) Voltage AC500V (50~60Hz, current 2mA) 60 $\pm$ 5 seconds, measured between adjacent terminals	无绝缘破坏现象 No insulation damage phenomenon
3.4	静电容量 Electrostatic capacity	1MHz $\pm$ 10KHz相邻两个端子之间测定 Measurement between adjacent terminals at 1MHz $\pm$ 10KHz	Max 5PF

4. 机械性能 Mechanical performance:

itme	Name	Test conditions	Spec
4.1	推力 thrust	推钮向操作方向平行推移 Push the button parallel to the direction of operation	500gf MAX

4.2	端子强度 Terminal strength	端子前端任意方向：静止施压 500 gf, 60±5秒，每次一个端子 Terminal front and in any direction: apply static pressure of 500gf, 60±5 seconds, one terminal at a time	端子无严重脱落破损，无严重松脱端子轻微弯曲可接受,四项电气性能符合 The terminals are not severely detached or damaged, and slight bending of the terminals is acceptable. The four electrical properties meet the requirements
4.3	操作强度 Operating intensity	1. 向推钮操作方向施压 2. 向推钮横向施压 3. 向推钮垂直施压 压力强度 1kg 时间 15 秒 1.Apply pressure in the direction of the push button operation 2.Apply lateral pressure to the push button 3.Apply pressure vertically to the push button Pressure intensity 1kg, time 15 seconds	端子无严重松脱，弯曲，或机械异常 四项电气性能符合 The terminals are not severely loose, bent, or mechanically abnormal. The four electrical properties meet the requirements
4.4	耐震性 Shock resistance	震动周波数 :10 ~ 55Hz 震动幅度 :1.5 mm 震动周期 :10 ~ 55 ~ 10(Hz)60 ±5 秒 周期震动变化方法:对数又与直线近似 震动方向:推钮操作方向、横向、垂直三种方向 Vibration frequency: 10~55Hz Vibration amplitude: 1.5mm Vibration period:10~55~10 (Hz) 60±5 seconds Vibration method: logarithmic and approximate to a straight line. Vibration direction: push button operation direction, lateral and vertical direction	接触阻抗 :Max 100mΩ 绝缘阻抗 :Min 10MΩ 耐电压 :AC500V,60 ±5 秒(50~60Hz 电流 2mA) 无绝缘破坏现象 推力:20 ~ 500gf 推力规格误差 30% 内, 无外观及构造异常 Contact impedance:Max 100mΩ Insulation impedance:Min 10MΩ Voltage withstand:AC 500V 60±5 seconds (50-60Hz current 2mA) Noinsulation damage phenomenon Thrust:20~500gf Thrust specification error within 30%,with no appearanceor structural abnormalities
4.5	着锡性 Tinning property	焊锡温度 :255 ±5℃ 浸渍时间 :3 ±0.5 秒 Soldering temperature: 255 ± 5 °C Immersion time: 3 ± 0.5 seconds	浸渍部份,着锡率 75% 以上 The impregnation part has a tin deposition rate of over 75%

4.6	耐焊性 soldering resistance	自动焊锡炉 产品放置于电路板表面温度 $240\pm5^{\circ}\text{C}$，时间 5 ± 1 秒，推钮置于 ON 的位置，进行焊锡作业 手工焊锡 产品放置于电路板,使用 30W 陶瓷控温 烙铁 焊着,温度控制于 $320^{\circ}\text{C}\pm5^{\circ}\text{C}$，焊接时 间每 3 秒以 内. Automatic soldering furnace Place the product on the surface of the circuit board at a temperature of $240\pm5^{\circ}\text{C}$ for 5 ± 1 second, and place the push button in the O N position for soldering operation Hand Soldering The product is placed on the circuit board and soldered with a 30W ceramic temperature controlled soldering iron. The temperature is controlled at $320^{\circ}\text{C}\pm5^{\circ}\text{C}$, and the soldering time is within 3 seconds	接触阻抗 :Max 100mΩ 绝缘阻抗 :Min 10MΩ 耐电压 :AC500V,60 ± 5 秒(50~60Hz 电流 2mA) 无绝缘破坏现象 推力:20 ~ 500gf 推力规格误差 30% 内, 无外观及构造异常 Contact impedance:Max 100mΩ Insulation impedance:Min 10MΩ Voltage withstand:AC 500V 60±5 seconds (50-60Hz current 2mA) Noinsulation damage phenomenon Thrust:20~500gf Thrust specification error within 30%,with no appearanceor structural abnormalities
-----	-----------------------------	---	--

5.耐候性Weathering resistance

Item	Name	Test conditions	Spec
5.1	耐寒性 cold resistance	置于温度 $-40\pm2^{\circ}\text{C}$ 内 250 小时后,放置于 常温常湿中 1 小时,并于 1 小时 内测定(开 关于水滴去除状态下) After being placed at a temperature of $-40\pm2^{\circ}\text{C}$ for 250 hours, place it in normal temperature and humidity for 1 hour, and measure it within 1 hour (under the condition of water droplet removal)	接触阻抗 :M ax 100 m Ω 绝 缘阻抗 :M in 100 M Ω 耐电压 :AC500V ,60 ±5 秒 (50~60Hz 电流 2mA) 无绝缘破坏现象 推力 :20 ~500gf 推力规格误差 30% 内, 无 外观及构造异常 Contact impedance:Max 100mΩ Insulation impedance:Min 10MΩ Voltage withstand:AC 500V 60±5 seconds (50-60Hz current 2mA) Noinsulation damage phenomenon Thrust:20~500gf Thrust specification error within 30%, with no appearanceor structural abnormalities

5.2	耐热性 heat resistance	置于温度 $85 \pm 2^{\circ}\text{C}$ 内 250 小时后, 放 置 于 常 温 常 湿 中 1 小 时, 并 于 1 小 时 以 内 测 定 After being placed at a temperature of $85 \pm 2^{\circ}\text{C}$ for 250 hours, place it in normal temperature and humidity for 1 hour, and measure it within 1 hour	接触阻抗:Max 100mΩ 绝缘阻抗:Min 100MΩ 耐电压:AC500V,60±5秒 (50~60Hz电流2mA)无绝缘破坏现象 推力规格误差30%内, 推力:20-500gf 无外观及构造异常 Contact impedance:Max 100mΩ Insulation impedance:Min 10MΩ Voltage withstand:AC 500V 60±5 seconds (50-60Hz current 2mA) Noinsulation damage phenomenon Thrust:20~500gf Thrust specification error within 30%, with no appearance or structural abnormalities
5.3	耐湿性 moisture resistance	置于温度 $40 \pm 2^{\circ}\text{C}$, 相对湿度 90 ~ 95%, 250 小时后, 置于常温常湿中 1 小时, 并于 1 小时以内测定 (开关于水滴去除状态下) Place at a temperature of $40 \pm 2^{\circ}\text{C}$ and a relative humidity of 90~95%. After 250 hours, place in a normal temperature and humidity environment Hour and measure within 1 hour (Regarding the state of water droplet removal)	接触阻抗 :Max 100mΩ 绝缘阻抗 :Min 10MΩ 耐 电 压 :AC500V, 60 ±5 秒 (50~60Hz 电 流 2mA) 无 绝 缘 破 坏 现 象 推 力 :20 ~ 500gf 推 力 规 格 误 差 30% 内, 无 外 观 及 构 造 异 常 Contact impedance:Max 100mΩ Insulation impedance:Min 10MΩ Voltage withstand:AC 500V 60±5 seconds (50-60Hz current 2mA) Noinsulation damage phenomenon Thrust:20~500gf Thrust specification error within 30% ,with no appearance or structural abnormalities
5.4	盐雾试验 Salt spray test	温度 $35 \pm 2^{\circ}\text{C}$, 盐水浓度 $5 \pm 1\%$ (重 量 比) 恒温槽内放置 48 ± 1 小时 验后以清水冲洗 Temperature $35 \pm 2^{\circ}\text{C}$, salt water concentration $5 \pm 1\%$ (by weight), placed in a constant temperature bath for 48 ± 1. After the test, rinse with clean water	无妨碍机能锈蚀状态 Unobstructed functional corrosion status

5.5	温度循环试验 Temperature cycling test	循环条件必须符合常温,常湿状态之下,样品处于正常状况,放置 1 小时后,并于 1 小时内测定 $85^{\circ}\text{C} \pm 2^{\circ}\text{C}$ $20^{\circ}\text{C} \pm 2^{\circ}\text{C}$ $-25^{\circ}\text{C} \pm 2^{\circ}\text{C}$ The cycling conditions must comply with normal temperature and humidity conditions, and the sample must be in normal condition. After being left for 1 hour, it should be measured within 1 hour $85^{\circ}\text{C} \pm 2^{\circ}\text{C}$ $20^{\circ}\text{C} \pm 2^{\circ}\text{C}$ $-25^{\circ}\text{C} \pm 2^{\circ}\text{C}$	接触阻抗 :Max 100mΩ 绝缘阻抗 :Min 10MΩ 耐电压:AC500V ,60±5秒 (50~60Hz 电流 2mA) 无绝缘破坏现象 推力:20 ~ 500gf 推力规格误差 30% 内, 无外观及构造异常 Contact impedance:Max 100mΩ Insulation impedance:Min 10MΩ Voltage withstand:AC 500V 60±5 seconds (50-60Hz current 2mA) Noinsulation damage phenomenon Thrust:20~500gf Thrust specification error within 30% ,with no appearance or structural abnormalities
-----	------------------------------------	--	---

6.耐久性 Durability

item	name	Test conditions	Spec
6.1	寿命试验 无负载 Life test without load	每分钟 15-20 次 连续 ON ← → OFF 动作 3000 次 15-20 times per minute 3000 consecutive ON←→OFF actions	接触阻抗 :Max 100mΩ 绝缘阻抗 :Min 10MΩ 耐电压:AC500V ,60±5秒 (50~60Hz 电流 2mA) 无绝缘破坏现象 推力:20 ~ 500gf 推力规格误差 30% 内, 无外观及构造异常 Contact impedance:Max 100mΩ Insulation impedance:Min 10MΩ Voltage withstand:AC 500V 60±5 seconds (50-60Hz current 2mA) Noinsulation damage phenomenon Thrust:20~500gf Thrust specification error within 30%, with no appearance or structural abnormalities

6.2	寿命试验 有负载 Life test with load	DC 24V 25m A每分钟 15~20 次 连续 ON ← → OFF动作2000 次 DC 24V 25m A 15~20 times per minute, continuous O N ←→ O FF action 2000 times	接触阻抗 :Max 100mΩ 绝缘阻抗 :Min 10MΩ 耐电压:AC500V,60±5秒 (50~60Hz 电 流 2mA) 无绝缘破坏现象 推力:20~500gf 推力规格误差 30% 内, 无 外观及构造异常 Contact impedance:Max 100mΩ Insulation impedance:Min 10MΩ Voltage withstand:AC 500V 60±5 seconds (50-60Hz current 2mA) Noinsulation damage phenomenon Thrust:20~500gf Thrust specification error within 30%,with no appearanceor structural abnormalities
-----	---------------------------------------	---	---