









REV.	ECR#	DESCRIPTION	DATE	DRAWN	CHECKED	APPROVED



- 备注:
- 1.材质:
- 1.1 胶芯: PA9T
- 1.2 端子: 高导电 C7025 ,
- 1.3 外壳: SUS304,
- 1.4 中夹片: SUS301,
- 2.主要特性:
- 2.1 额定电流: 5A
- 2.2 接触阻抗: 40mΩ MAX(初始值)
50mΩ MAX(测试后)
- 2.3 绝缘阻抗: 100MΩ MIN
- 2.4 耐压测试: 100V AC R.M.S.
- 2.5 整体插入力: 5-20N 整体插入力: 5-20N (耐久后)
整体拔出: 8-20N 整体拔出: 6-20N (耐久后)
- 2.6 耐久: 10000 次
- 2.7 耐高温: SMT 回流焊 (峰值 260°±5°), 塑胶不能有起泡,
融胶等不良, 变色, 翘曲变形在公差范围以内;
- 2.8 产品须做焊锡测试, 粘锡面积达到 95% 以上;
- 3.0 盐雾测试: 48H MIN
- 3.1 工作温度: -30℃ ~ +85℃



PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A2	SSTXp1	B11	SSRXp1
A3	SSTXn1	B10	SSRXn1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	SSRXn2	B3	SSTXn2
A11	SSRXp2	B2	SSTXp2
A12	GND	B1	GND

料号编码:

WTT - XX X X X XXX XX XX

公司品牌

内部编码

产品流水号

产品系列

CG:常规系列
FS:防水系列
DT:外壳带弹片系列
WZ:无定位柱系列

沉板高度
080:0.8H
100:1.0H
160:1.6H
以此类推




上板类型
A:立式
B:卧式
C:侧立式
以此类推

产品结构
A:立式
B:卧式
C:侧立式
以此类推

PIN 数
06:6P
16:16P
24:24P
以此类推

产品系列
M:公座系列
F:母座系列

RECOMMENDED PCB LAYOUT(TOP VIEW)


Part Number		Product Description				
WTT-04F24BC100CG42		TYPE-C 24PIN on-board four-pin recessed 1.0 terminal double-row SMD female connector L7.90MM				
CUSTOMER DRAWING						
DRAWN	Zhang Xincheng	Tolerances (Except as Noted) GENERAL TOLERANCE: X. ± 0.40 X.X ± 0.30 X.XX ± 0.20 X.XXX ± 0.10	Units: Metric (mm)  3rd Angle Projection	 COMPLIANT 2017 UL LLC UL94V-0	 RoHS COMPLIANT 2011/05/EU Deca-BDE	 REACH COMPLIANT 2011/07/26/2008 SVHC
CHECKED	Xiong fangyuan					
APPROVED	Huangshaohuang					
Drawing Date	22/05/24					




用心连接世界

SCALE 1:1	SIZE: A4	SHEET: 1 or 2
--------------	-------------	------------------

REV.	ECR#	DESCRIPTION	DATE	DRAWN	CHECKED	APPROVED



包装示意图:



- 备注:
- 1.把上下载带送入载带机进行调整,然后将产品按照指定的方式摆入下载带中,开动卷带机进行卷装(每卷包1000PCS),卷装完成后需用上带缠绕最少20CM;
 - 2.在卷装OK的每卷盘面的指定位置上贴上物料和RoHS标签装入纸箱内;每箱装10盘
 - 3.纸箱用封箱带将其封好,胶带要求工字型,不可遮住标签;
 - 4.如果客户对包装标签另有要求,请按客户要求作业;有未满足之零数箱需用缓冲材料填充;
 - 5.上载带剥离力:0.2-1.2N.;

Part Number		Product Description				
WTT-04F24BC100CG42		TYPE-C 24PIN on-board four-pin recessed 1.0 terminal double-row SMD female connector L7.90MM				
CUSTOMER DRAWING						
DRAWN	Zhang Xincheng	Tolerances (Except as Noted) GENERAL TOLERANCE: X. ± 0.40 X.X ± 0.30 X.XX ± 0.20 X.XXX ± 0.10	Units: Metric (mm)			
CHECKED	Xiong fangyuan		 3rd Angle Projection			
APPROVED	Huangshaohuang					
Drawing Date	22/05/24					

WTT®

用心连接世界

SCALE	SIZE:	SHEET:
1:1	A4	2 or 2