

SOP-8 Plastic-Encapsulate MOSFETS

Features

- $V_{DS}=-30V$
- $I_D=-11.5A$
- $R_{DS(on)}@V_{GS}=-10V < 14m\Omega$
- $R_{DS(on)}@V_{GS}=-4.5V < 20m\Omega$
- Advanced Trench Technology
- Switching Speedze
- Low Gate Charge and Rdson

Drain-source Voltage
-30 V
Drain Current
-11.5 Ampere


Applications

- PWM Application
- Load Switch
- Power Mangement

Mechanical Data

- Case: SOP-8
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant,halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750,Method 2026

Function Diagram



Ordering Information

PACKAGE	PACKAGE CODE	UNIT WEIGHT(g)	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
SOP-8	R3	0.077	4000	8000	64000	13"

Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	VALUE
Drain-source Voltage	V_{DS}	V	-30
Gate-source Voltage	V_{GS}	V	± 20
Drain Current	I_D	A	-11.5
Pulsed Drain Current ⁽¹⁾	I_{DM}	A	-46
Total Power Dissipation	P_D	W	3
Single Pulse Avalanche Energy ⁽²⁾	E_{AS}	mJ	64
Junction temperature	T_J	°C	-55 ~+150
Storage temperature	T_{stg}	°C	-55 ~+150
Thermal Resistance Junction-to-Ambient ⁽³⁾	$R_{\theta JA}$	°C / W	41.6

● Static Parameter Characteristics (Tj=25°C Unless otherwise specified)

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Drain-Source Breakdown Voltage	BV_{DSS}	$V_{GS}=0V, I_D=-250\mu A$	V	-30	—	—
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS}=-30V, V_{GS}=0V$	μA	—	—	-1.0
Gate-Body Leakage Current	I_{GSS}	$V_{GS}=\pm 20V, V_{DS}=0V$	nA	—	—	± 100
Gate Threshold Voltage ⁽⁴⁾	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=-250\mu A$	V	-1.0	-1.5	-2.5
Static Drain-Source On-Resistance ⁽⁴⁾	$R_{DS(on)}$	$V_{GS}=-10V, I_D=-8A$	m Ω	—	10	14
		$V_{GS}=-4.5V, I_D=-2A$		—	14	20

● Dynamic Parameters

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Input Capacitance	C_{iss}	$V_{DS}=-15V, V_{GS}=0V, f=1MHz$	pF	—	2040	—
Output Capacitance	C_{oss}			—	260	—
Reverse Transfer Capacitance	C_{rss}			—	245	—

● Switching Parameters

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Turn-on Delay Time	$t_{D(on)}$	$V_{GS}=-10V, V_{DD}=-15V, I_D=-10A, R_{GEN}=3\Omega$	nS	—	7	—
Turn-on Rise Time	t_r		nS	—	6	—
Turn-off Delay Time	$t_{D(off)}$		nS	—	112	—
Turn-off fall Time	t_f		nS	—	78	—
Total Gate Charge	Q_g	$V_{DS}=-15V, I_D=-10A, V_{GS}=-10V$	nC	—	59	—
Gate-Source Charge	Q_{gs}		nC	—	10	—
Gate-Drain Charge	Q_{gd}		nC	—	14	—

● Drian-Source Diode Characteristics







PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Diode Forward Voltage ⁽⁴⁾	V_{SD}	$I_S=-11.5A, V_{GS}=0V$	V	—	—	-1.2
Maximum Body-Diode Continuous Current	I_S	—	A	—	—	-11.5
Reverse Recovery Time	t_{rr}	$I_F=-10A, di/dt=100A/\mu S$	nS	—	21	—
Reverse Recovery Charge	Q_{rr}		nC	—	10	—

Note :






(1) Repetitive Rating: Pulse width limited by maximum junction temperature.

(2) EAS condition : Tj=25°C, V_{DD}=-15V, V_G=-10V, L=0.5mH, I_{AS}=-16A, R_g=25 Ω .(3) Surface mounted on 1inch² FR-4 board with 20Z copper.(4) Pulse Test: Pulse Width $\leq 300\mu s$, Duty Cycle $\leq 0.5\%$.


● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)




● **Ratings And Characteristics Curves** ($T_a=25^\circ\text{C}$ Unless otherwise specified)




● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)





● Package Outline Dimensions (SOP-8)





● Suggested Pad Layout





1. Gate Charge Test Circuit & Waveforms



2. Resistive Switching Test Circuit & Waveforms



3. Unclamped Inductive Switching (UIS) Test Circuit & Waveforms



4. Diode Recovery Test Circuit & Waveforms

