






版次	变更摘要	日期	序号	品名	材质
1	增加料号说明	2015/1/28			

①	0.5拉拔3代胶芯 (H2.0)	LCP UL94V-0 本色
②	0.5拉拔立式端子	磷青铜/表面镀锡
③	0.5拉拔卧式3代后盖 (H2.0)	LCP UL94V-0 黑色
④	0.5拉拔3代焊片 (H2.0)	黄铜/表面镀锡




CKT	DIM A	DIM B	DIM C	DIM D
4	1.50	2.56	7.60	
5	2.00	3.06	8.10	
6	2.50	3.56	8.60	
7	3.00	4.06	9.10	
8	3.50	4.56	9.60	
9	4.00	5.06	10.10	
10	4.50	5.56	10.60	
11	5.00	6.06	11.10	
12	5.50	6.56	11.60	
13	6.00	7.06	12.10	
14	6.50	7.56	12.60	
15	7.00	8.06	13.10	
16	7.50	8.56	13.60	
17	8.00	9.06	14.10	
18	8.50	9.56	14.60	
19	9.00	10.06	15.10	
20	9.50	10.56	15.60	
21	10.00	11.06	16.10	
22	10.50	11.56	16.60	
23	11.00	12.06	17.10	
24	11.50	12.56	17.60	
25	12.00	13.06	18.10	
26	12.50	13.56	18.60	
27	13.00	14.06	19.10	
28	13.50	14.56	19.60	
29	14.00	15.06	20.10	
30	14.50	15.56	20.60	
31	15.00	16.06	21.10	
32	15.50	16.56	21.60	
33	16.00	17.06	22.10	
34	16.50	17.56	22.60	

东莞市文章济美电子有限公司

品名 (TITLE)	0.5 Pitch 拉拔立式3代正脚位1代	制图 (DR)	
料号 (DWG.NO)	5001-FCZ0544-**-G1-00-B	校对 (CHKD)	
比例 (SCALE)	1:1	审核 (APPD)	
单位 (UNITS)	mm	张数 (SHEET)	1 OF 2
		SIZE	A4
		REV	A



一般公差 (TOLERANCE)
X ±0.50 XX ±1.0
X ±0.20 XXX ±0.05
ANGLES ±1°



技术指标:

- 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
- 温度范围: -25° C~85° C.
- 额定电压: 50V, AC/DC(等效).
- 接触电阻: ≤0.03Ω.
- 绝缘电阻: ≥500MΩ
- 产品料号:

5001—FCZ 05 44 —** G 1-00

立式正脚
Pitch::0.5
Height:4.4
Pin

ALTERNATE
Packing: G (卷)
T (管)