FSPTVSHC3D4V5BH

1-Line Bi-directional TVS Diode

Features


- Small SOD-323 package
- Protects one data or power line
- Working Voltage: 4.5V
- High peak pulse current capability
- Ultra low clamping voltage
- Complies with following standards:
  - – IEC 61000-4-2 (ESD) immunity test
    - Air discharge: ±30kV
    - Contact discharge: ±30kV
  - – IEC61000-4-5 (Lightning) 180A (8/20μs)
- RoHS Compliant



SOD-323

Mechanical Characteristics

- Package: SOD-323
- Lead Finish: Sn
- Case Material: “Green” Molding Compound.
- Terminal Connections: See Diagram Below
- Marking Information: See Below



Circuit diagram

Applications

- Mobile Phones and Accessories
- Battery Protection
- USB VBus
- Power Line Protection
- Hand Held Portable Applications



48D= Device code

Marking (Top View)

Ordering Information

Part Number	Packaging	Reel Size
FSPTVSHC3D4V5BH	3000/Tape & Reel	7 inch


Absolute Maximum Ratings (T_A=25°C unless otherwise specified)

Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20μs)	Ppk	2700	W
Peak Pulse Current (8/20μs)	Ipp	180	A
ESD per IEC 61000−4−2 (Air) ESD per IEC 61000−4−2 (Contact)	V_{ESD}	±30 ±30	kV
Operating Temperature Range	T_J	−55 to +125	°C
Storage Temperature Range	Tstg	−55 to +150	°C


Electrical Characteristics (T_A=25°C unless otherwise specified)

Parameter	Symbol	Min	Typ	Max	Unit	Test Condition
Reverse Working Voltage	V_{RWM}			4.5	V	
Breakdown Voltage	V_{BR}	4.6	5.2	6.0	V	I_T = 1mA
Reverse Leakage Current	I_R			1.0	μA	V_{RWM} = 4.5V
Clamping Voltage	V_C		11	14	V	I_{PP} = 100A (8 x 20μs pulse)
Clamping Voltage	V_C		18	20	V	I_{PP} = 180A (8 x 20μs pulse)
Junction Capacitance	C_J		275		pF	VR = 0V, f = 1MHz


Typical Performance Characteristics (T_A=25°C unless otherwise Specified)




Junction Capacitance vs. Reverse Voltage




Peak Pulse Power vs. Pulse Time




Clamping Voltage vs. Peak Pulse Current (tp = 8/20μs)



Power Derating Curve



8 X 20μs Pulse Waveform




Note：Data is taken with a 10x attenuator

ESD Clamping Voltage


8 kV Contact per IEC61000−4−2

SOD-323 Package Outline Drawing



	MILLIMETERS		
	MIN	NOM	MAX
A	0.800	- -	1.100
A1	0.800	- -	0.900
A2	0.000	- -	0.100
b	0.250	- -	0.400
c	0.080	- -	0.177
D1	1.600	1.700	1.800
D	2.300	- -	2.800
E	1.150	- -	1.400
L	0.475REF		
L1	0.100	- -	0.500
Θ	0°	- -	8°

Suggested Land Pattern



Unit：mm