

RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2026.07.31

SPECIFICATIONS

- 1.Voltage rating: 50V AC, DC
- 2.Current rating: 2A AC, DC
- 3.Temperature range: -25°C ~ +85°C
- 4.Insulation resistance: 1000MΩ Min.
- 5.Withstanding voltage: 500V AC/ minute.
6. Contact resistance: 20mΩ Max.

Material:

Material:Phosphor Bronze

Finish: Plated Tin or Plated Gold

Applicable wire: AWG#32-#28

Mate with P1201 series housing



Qty/Reel: 15000PCS

Ordering Code:


T1201PS-00
1 2

1.序列号

2.00=镀金





SECTION A-A



SECTION B-B



SECTION D-D



WIND OPERATION
AFTERSTAMPING AND
BEFOREPLATING

WIND OPERATION
AFTERPLATING AND
BEFOREASSEMBLY

X.±0.50	X.°±	PART NO: T1201PS-00		XFCN 兴飞连接器		
.X±0.25	.X°±					
.XX±0.15	.XX°±	TITLE: 1.20mm Crimp Style Connectors		0769-82001899		
.XXX±0.10	.XXX°±			www.xfconn.com		
UNITS:	mm			DWG NO: /		
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED,COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN		APPD	Chen ZhiQiang			
		CHKD	Liu Wei	VIEW		
		DRAW	Chen HongJiang	SCALE	SHEET	REV
		DATE	2026.07.31	NONE	1/1	A1