





C



G-Switch

Series No

Connector
W-Wafer

Angle
V-180°

Termipoint
D-DIP

Terminal Plating
BT-Bright Tin

— **Housing Colour**
W-White

—Pin Q' PY
06~08

—Row NO
2-Dual Dows

G-Switch Specification:

- 1.Current rated: 5.0A AC/DC
- 2.Voltage rating: 100V AC/DC
- 3.Withstanding voltage:1000V AC
- 4.Contact resistance: 10mΩ max.
- 5.Insulation resistance: 1000MΩ min
- 6.Durability cycle: 50Cycles
- 7.Removal force: 3.5kgf/Pin min
- 8.Operating temperature range: -55℃ ~ +105℃
- 9.Waterproof grade:IP68(Anti immersion type)

Ordering Information:

Circuit	Dimensions(mm)		Circuit	Dimensions(mm)	
	A	B		A	B
06	4.00	9.80	08	6.00	11.80

SCALE: 1:1	UNIT: mm	Title: Wafer 2.00mm Pitch 180° DIP With Lock Type Dual Dows Connector			
SIZE: A4					
Unless otherwise General Tolerance: X ±0.40 X.x ±0.30 X.xx ±0.20 X* ±5° X° ±3°		Molde Code: GT-C2001WVD-2XXXXXX01			
		DRAWN	CHECKED	APPROVED	DATE
		Hu	Chen	Chen	2021.10.20

 品赞科技
www.dg-switch.com

REV: A0	SHEET: 1/1
---------	------------