







REV.	REVISION DESCRIPTION	DATE




- NOTES:
- 1. Rated voltage: 250V AC.DC
 - 2. Rated current: 3A AC DC
 - 3. Contact resistance: $\leq 20 \text{ m}\Omega$
 - 4. Insulation resistance: $\geq 500 \text{ M}\Omega$
 - 5. Withstand voltage: 1100V AC/minute
 - 6. Ambient temprature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
 - 7. Material :Nylon UL94V-0

Circuits	Product name	Dimension mm		Circuits	Product name	Dimension mm	
		A	B			A	B
2	QAC-H-2AS	2.50	7.90	9	QAC-H-9AS	20.00	25.40
3	QAC-H-3AS	5.00	10.40	10	QAC-H-10AS	22.50	27.90
4	QAC-H-4AS	7.50	12.90	11	QAC-H-11AS	25.00	30.40
5	QAC-H-5AS	10.00	15.40	12	QAC-H-12AS	27.50	32.90
6	QAC-H-6AS	12.50	17.90	13	QAC-H-13AS	30.00	35.40
7	QAC-H-7AS	15.00	20.40	14	QAC-H-14AS	32.50	37.90
8	QAC-H-8AS	17.50	22.90	15	QAC-H-15AS	35.00	40.40

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO .,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: QAC-H-AS		TITLE: 2.50 mm Pitch Wire To Board DIP Wafer	
.XX: ± 0.15	.X° : ± 2.0°				
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:25/03/25	PART NO:	
FINISH: _____		CHKD: Wu Hui	DATE:25/03/25		
DRAWING NO:		APPD: Ren An De	DATE:25/03/25	SCALE: N/A	PAGE: 1/1
				UNITS: mm	REV. : A






REV.	REVISION DESCRIPTION	DATE	APPD

NOTES:

Rated voltage: 250V AC.DC
Rated current: 3A AC DC
Contact resistance: $\leq 20\text{ m}\Omega$
Insulation resistance: $\geq 500\text{ M}\Omega$
Withstand voltage: 1100V AC/minute
Ambient temperature: $-40^{\circ}\text{C}\sim +105^{\circ}\text{C}$
Wire range: AWG#26~#20
Materials:
Terminal: Phosphor bronze,Tin plated
Used in QAC-Y Series Housing.
Qty/Reel:6,000 PCS

Product name	Dimension mm				适用线规AWG
	A1	B1	A2	B2	
QAC-T-G	2.4	2.4	2.0	1.7	#22-20
QAC-T	2.2	2.4	1.8	1.5	#26-22

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	X°: $\pm 3.0^{\circ}$	PRODUCT NAME: QAC-T		TITLE: 2.00 mm Pitch Crimp Terminal	
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DR:Chen Quan Long	DATE:25/03/26	PART NO:	
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	CHKD: Wu hui	DATE:25/03/26	SCALE: N/A	PAGE: 1/1
FINISH: 		APPD:Ren An De	DATE:25/03/26	UNITS: mm	REV.: A
DRAWING NO:					