




3D VIEW




推荐选5#:7#端为检测PIN

SCHEMATIC



RIGHT PACKING P.C.B LAYOUT
TOP VIEW



(Ø3.50mm 3 OR 4 POLE PLUG DETAIL DRAWING)

- NOTES:

1. CONTACT CURRENT RATING:1A;
2. CONTACT RESISTANCE:50mΩ MAX;
3. INSULATION RESISTANCE:100MΩ MIN;
4. DIELECTRIC WITHSTANDING:500V AC MIN;
5. DURABILITY:5000CYCLES MIN;
6. CONNECTOR MATING FORCES:2.94~29.4N(0.3~3.0kgf);
7. CONNECTOR UNMATING FORCES:2.94~29.4N(0.3~3.0kgf);

07	CONTACT F	1 PCS	PHOSPHOR BRONZE, T=0.20	Au Plated
06	CONTACT E	1 PCS	PHOSPHOR BRONZE, T=0.20	Au Plated
05	CONTACT D	1 PCS	PHOSPHOR BRONZE, T=0.20	Au Plated
04	CONTACT C	1 PCS	PHOSPHOR BRONZE, T=0.20	Au Plated
03	CONTACT B	1 PCS	PHOSPHOR BRONZE, T=0.20	Au Plated
02	CONTACT A	1 PCS	PHOSPHOR BRONZE, T=0.20	Au Plated
01	HOUSING	1 PCS	HIGH TEMPERATURE PLASTIC	BLACK
ITEM	PART NAME	Q'TY	MATERIAL	DESCRIPTION



深圳市华宇创精密电子有限公司

TOLERANCE:		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME:	
X.X ±0.30				PJ-342 无头单柱 前两插后四贴	
X.XX ±0.25		CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW02-PJ342F-290B
X.XXX ±0.15				MOLD NO.	
X.* ±2* X.* ±0.5*		APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO:	HYC-2609221146
				SHEET NO.	1 OF 1
UNIT: mm [inch]					
SCALE:1:1	SIZE: A4				