




SECTION:A-A



SECTION:B-B



GT-C2001 T F -X XX 1

G-Switch

Series No

Connector
T-Terminal

Terminal Plating
BT-Bright Tin
11-All G/F

Metal
H-High Conductivity
Copper Alloy

F-Female

G-Switch Specification:

- 1.Current rated: 5.0A AC/DC
- 2.Voltage rating: 100V AC/DC
- 3.Withstanding voltage:1000V AC
- 4.Contact resistance: 10mΩ max.
- 5.Insulation resistance: 1000MΩ min
- 6.Durability cycle: 50Cycles
- 7.Removal force: 3.5kgf/Pin min
- 8.Operating temperature range: -55°C ~ +105°C
- 9.Waterproof grade:IP68(Anti immersion type)

GT-C2001TF-H111	High Conductivity Copper Alloy	All G/F	AWG#20~#26	1.80mm(Max)	10000
GT-C2001TF-HBT1	High Conductivity Copper Alloy	Bright Tin	AWG#20~#26	1.80mm(Max)	10000
Part NO	Material	Plating	Wire Size	Insulation O.D	Reel/PCS



SCALE: 1:1 UNIT: mm
SIZE: A4

Unless otherwise
General Tolerance:
X ±0.40
X.x ±0.30
X.xx ±0.20
X* ±5°
X.x° ±3°

Title: Terminal 2.00mm Pitch JWPF
Crimp Style Female

Molde Code: GT-C2001TF-XXX1

DRAWN	CHECKED	APPROVED	DATE
Hu	Hu	Chen	2021.10.20

品赞科技
b-Switch
www.dg-switch.com

REV: A0 SHEET: 1/1