









REV.	ECR#	DESCRIPTION	DATE	DRAWN	CHECKED	APPROVED




A1	GND	B12	GND
A2		B11	
A3		B10	
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	D+	B7	D-
A7	D-	B6	D+
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10		B3	
A11		B2	
A12	GND	B1	GND



- 特性:
- 一、电气性能: EICTRICAL
 - 1.额定电流: 5.0A
 - 2.接触阻抗: 40 MILLIOHMS MAX
 - 3.耐电压: 100V AC / 1 mA MAX
 - 4.绝缘阻抗: 150V DC/100 MEGA OHMS MIN
 - 二、机械性能:
 - 1.插入力: 5~20N; 拔出力: 8~20N 2.使用寿命: 10000次
 - 三、材料: MATERIAL
 - 1.外壳:SUS304 T=0.30mm 2.中夹片: SUS301 T=0.15mm
 - 3.端子: C7025 T=0.15mm 4.塑胶 (见BOM)
 - 四、电镀:FINISH
 - 1.端子: 接触点镀金1u"
PIN脚焊接区域镀金G/F
 - 2.外壳: 镀镍50u"Min
 - 五、电镀品需做粘锡测试: 粘锡面积达到95%以上。
 - 六、SMT回流焊 (峰值260°C±5°C) 不能起泡、熔胶、变色不良 (变形在公差范围以内)
 - 七、工作温度: -55°C~+85°C
 - 八、盐雾测试: 通过24H在浓度为5±1%盐水的盐雾测试无生锈现象

RECOMMENDED PCB LAYOUT (TOP VIEW)


Part Number		Product Description				
WTT-06F16CV458CG45		TYPE-C 16PIN Side-Mount SMD CH4.58MM				
CUSTOMER DRAWING						
DRAWN	Zhang Xincheng	Tolerances (Except as Noted) GENERAL TOLERANCE: X. ± 0.35 X.X ± 0.25 X.XX ± 0.15 X.XXX ± 0.10	Units: Metric (mm)	 COMPLIANT 2017 UL LLE UL94V-0	 RoHS COMPLIANT 2011/05/EU Deca-BDE	 REACH COMPLIANT 2013/06/06 SVHC
CHECKED	Xiong fangyuan					
APPROVED	Huangshaohuang					
Drawing Date	22/05/24					
		 3rd Angle Projection				

WTT®



用心连接世界

SCALE 1:1	SIZE: A4	SHEET: 1 or 2
--------------	-------------	------------------


REV.	ECR#	DESCRIPTION	DATE	DRAWN	CHECKED	APPROVED



2. 上帶 剝力力為: 0.1~1.3N(10.2gf~130gf)
PEELING OFF FORCE OF TOP TAPE: 0.1~1.3N(10.2gf~130gf)
出貨'運輸過程中一定注意:
THIS REQUIREMENT SHOULD BE APPLIED AT SHIPMENT:
卷帶在運輸過程中不能散開
PEELING OFF SHOULD NOT BE ALLOWED DURING TRANSPORTATION



NOTE:
1. 每捲包裝數量及每箱裝箱數量如左下表格.
Packing q'ty of each reel & carton as below table shown.
2. 將裝滿產品的卷盤放入紙箱并以膠帶封口
Put reels in the carton and use adhesive tape to seal up.



DETAIL: A
10:1

載帶規格	φ380mm	包裝數量:	500PCS
產品單重	1.1g/pcs	產品淨重:	4.4kg
紙箱規格	390mmX390mmX310mm	包裝數量:	8盤 / 箱/(8.8kg)

Part Number		Product Description		
WTT-06F16CV458CG45		TYPE-C 16PIN Side-Mount SMD CH4.58MM		
CUSTOMER DRAWING				
DRAWN	Zhang Xincheng	Tolerances (Except as Noted)	Units:	
CHECKED	Xiong fangyuan	GENERAL TOLERANCE:	Metric (mm)	
APPROVED	Huangshaohuang	X. ± 0.35		
Drawing Date	22/05/24	X.X ± 0.25		
		X.XX ± 0.15		
		X.XXX ± 0.10		

WTT®

用心连接世界

SCALE 1:1	SIZE: A4	SHEET: 2 or 2
--------------	-------------	------------------