

REVISIONS (修正)			
NO. (序号)	DESCRIPTION(描述)	DCN NO.(变更号)	DATE(日期)
D.0	NEW RELEASE		

NOTE;

1. Material

Plunger: C3604

Barrel: C3604

Spring: SUS

2. Plating

Plunger: 3 micro-inch minimum Au
over 50~100 micro-inch nickel

Barrel : 1 micro-inch minimum Au
over 50~100 micro-inch nickel

3. Electrical

Rated current & voltage: DC12V; 1A.

Contact resistance: 100 mohm maximum
at working height(quiescence)

4. Mechanical

Spring force: 90g±25g at Normal working height




Durability: 10,000 cycles(minimum)

5. When the current is greater than 2A then need to increase the time delay circuit (3 second)

6.To ensure the best usage,please operate it based on the working height

Based on the engineering drawings, shall not exceed the maximum allowed compression

7.Products comply with ROHS standards



RECOMMEND PCB LAYOUT
Layout Tolerance: $\pm 0.05\text{mm}$

DRAW (设计)	LIAOYI	SCALE (比例)	10 : 1	UNIT (单位)	mm	DRAWING NO. (图号)	KTT40003UT01-R
COUNTER SIGN (会签)		SHEET (页数)	1 of 1	PROJECT (视图)		MATERIAL (材质)	Seeing notes (见备注)
AUDIT (审核)		DATE (日期)	2024.10.31	VER (版次)	D.0	TITLE (品名)	Pogo pin
APPROVE (核准)		PLATE (镀层)	Seeing notes(见备注)				
THE UNMARKED TOLERANCE ARE AS BELOW : (未标记的公差)				<div>东莞市柯睿电子有限公司</div> <div>Dong Guan KeRui Electronics Co,Ltd</div>			
LENGTH (尺寸)		ANGLE (角度)					
0~60	±0.05mm	0.	±2.0°	The information in this document is property of KeRui company and should not be copied or reproduced in any other way, without written permission.			
>6~30	±0.10mm	0.0	±1.0°				
>30~120	±0.15mm	0.00	±0.50°				