



RoHS Compliant

REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		










RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm



	A	B	C	D
DIM A	8.8	9.3	10.0	10.5

NOTES:
SPECIFICATION:
1. CURRENT RATING: 5.0A MAX
2. VOLTAGE: 100 VAC
3. TEMPERATURE RANGE: −30 °C ~ 85 °C
4. CONTACT RESISTANCE: 40 MILLIONHM MAX
5. INSULATION RESISTANCE: 100 MEGOHMS MIN.
6. LNSERTION FORCE : 5N~20N
7. UNMATING FORCE: 8N~20N
8. DURABILITY: 10,000 CYCLES

A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

NO.	DESCRIPTION	MATERIAL	REMARKS	QTY
6	SHELL	STAINLESS STEEL	NI/SN Plated	1PCS
5	SHIELDING PLATE	STAINLESS STEEL	---	1PCS
4	MD	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
3	CONTACT	COPPER ALLOY	Au/NI Plated	1SET
2	CONTACT	COPPER ALLOY	Au/NI Plated	1SET
1	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK	1PCS


X. ±0.50	X.° ± 2°	UNITS mm	广东创粤科技有限公司
.X ±0.30	.X° ± 1°	MAT'L	TITLE: TYPE-C 16PIN 立贴母座 H=8.65MM
.XX ±0.10	.XX° ± 0.5°		
.XXX ± 0.05		FINISH	TYPE-C-16P-H8.8SMT-08607 DWG NO.:
		Q'TY	CHKD:
			DR:

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD

SCALE	SHEET	REV.
1/1	1/1	A1

REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		


RoHS Compliant




① 产品入载带示意图




② 卷盘贴标签示意图



③ 10盘产品叠层示意图



④ 产品入外箱示意图



⑤ 外箱封箱示意图

NOTE:

1.QUANTITY/REEL:450 PCS
数量/卷:450 PCS
QUANTITY/INNER CARTON:450 X 10 = 4500 PCS
数量/箱: 450 X 10 = 4500 PCS

2.FREE 16 CAVE IN THE FRONT CARRIER ADN FREE 16 CAVE IN THE END CARRIER.
包装带内圈空16格,外圈空16格.

ITEM	DESC.	MATERIAL	REMARKS	QTY
1	成品		C TYPE母座成品	4500
2	CARRIER TAPE	PET	W=24mm T=0.50mm	7.7M
3	COVER TAPE	PET	W=13.3mm T=0.05mm	7.7M
4	小标签		L102mm*W59mm	10
5	卷盘	PS	ø380mm*H28.4mm	10
7	外标签		L102mm*W102mm	1
9	外箱	A=A	L395mm*W395mm*H300mm	1

X. ±0.50	X.° ± 2°	UNITS mm	广东创粤科技有限公司
.X ±0.30	.X° ± 1°		
.XX ±0.10	.XX° ± 0.5°	MAT'L	TITLE: TYPE-C 16PIN 立贴母座 H=8.65MM
.XXX ±0.05			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD		FINISH	TYPE-C-16P-H8.8SMT-08607 DWG NO.:
		Q'TY	CHKD:
			DR:

SCALE	SHEET	REV.
1/1	1/1	A1