


HAOYU





P.C.B LAYOUT



tel：0769-82310511-867
邮箱：hooya89@hooya.hk

SPECIFICATION
1.Rating : DC30V 0.5A.
2.Contact resistance: ≤100mΩ.
3.Insulation resistance: ≥100MΩ (DC500V).
4.Withstanding voltage: 500VAC .
5.INSERTION FORCE:≤30N
REMOVAL FORCE: 2 meters highdrop,battery noshedding
6.Life test: 1500 cycles.
7.Operation temperature range:-25℃~85℃.
8.Sign"* "is importance dimension.

NO.	PART NAME	MATERIAL	QTY	FINISHING
3	CONTACT FOOT	BRASS	1	Au-PLATED
2	SPRING	BRASS	1	Au-PLATED
1	CASE	PA6T	1	COFFEE

TOLERANCE UNLESS SPECIFIED
<1.5: ±0.1mm
>1.5~5.0: ±0.25mm
>5.0: ±0.3mm
ANGULAR ±1°

NO	DATE	REVISIONS	BY	APPD
1	2016.5.25	增加文字说明		

TITLE: LIN SERIES
MODEL: LIN-023
UNIT : MM
SCALE: 1:1
ROHS COMPLIANT
DWN
CHK'D
APPD
PRO.AGL:
REV: A1

DONGGUANG HAOYU ELECTRONICS CO., LTD
东莞市弘皓电子有限公司
皓宇 HOOYA