






ITEM	DIM A	形状	DIM B
SATA-020FB-22PS1BY	2.10		2.08
SATA-020F-22PS1BY	2.30		



SPECIFICATION:

1.MATERIAL:

1.1 HOUSING: LCP UL 94V-0

1.2 COLOR: BLACK

1.3 CONTACT: PHOSPHOR BRONZE C5191R-H, T=0.25mm

1.4 PEG: BRASS C2680R-H, T=0.30mm

2.FINISH:


2.1 CONTACT: 1~15u" GOLD PLATING ON CONTACT AREA

2.2 100u" TIN PLATING ON SOLDER TAILS

2.3 30u" NICKEL UNDERPLATING OVER ALL

2.4 PEG: 100u" TIN PLATING ON SOLDER TAILS

2.5 30u" NICKEL UNDERPLATING OVER ALL



RECOMMEND PCB LAYOUT (T=1.2)
PCB TOLERANCE: ±0.05

环境要求		产品必须符合ROHS要求	
3	Peg	Brass C2680	Tin/Ni Plated
2	Terminal	Pho.Bronze C5191R-H	Gold/Tin Plated
1	Housing	High Temp	Black
NO.	DESCRIPTION	MATERIAL	COLOR

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.30 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10

东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	SATA 7+15P 母座板下4.2SMT三条杠侧插鱼叉		
DWN	xiong	PART NO.	SATA-020F-22PS1BY
CHKD	lee	SCALE:1:1	UNIT: mm
APVD	wang	SIZE: A4	SHEET:10F 1

CUSTOMER COPY