



SPECIFICATION:

1.MATERIAL:

1.1 HOUSING: LCP UL 94V-0

1.2 COLOR:BLACK

1.3 CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm

1.4 PEG: BRASS C2680R-H,T=0.30mm

2.FINISH:







2.1 CONTACT: 1u"/3u"/5u"/15u" GOLD PLATING ON CONTACT AREA

2.2 100u" TIN PLATING ON SOLDER TAILS


2.3 30u" NICKEL UNDERPLATING OVER ALL

2.4 PEG:100u" TIN PLATING ON SOLDER TAILS

2.5 30u" NICKEL UNDERPLATING OVER ALL



ITEM	DIM A	形状	DIM B
SATA-025FB-22PS1BY	2.10		2.08
SATA-025F-22PS1BY	2.30		



RECOMMEND PCB LAYOUT (T=1.2)
PCB TOLERANCE: ±0.05

环境要求		产品必须符合ROHS要求		
3	Peg	Brass C2680R-H		Tin/Ni Plated
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD		
DECIMALS: ANGLES:		TITLE: SATA 7+15P 母座板下4.20SMT 不带右侧插式		
X	:±0.30	X	:±2°	DWN xiong PART NO. SATA-025F-22PS1BY
X.X	:±0.20	X.X	:±1°	CHKD lee SCALE:1:1 UNIT: mm
X.XX	:±0.10	APVD wang	SIZE: A4	SHEET:10F 1 REV: A4
CUSTOMER COPY				