

SPTECH Field Stop Trench IGBTs offer low switching losses, high energy efficiency and high avalanche ruggedness for soft switching applications such as inductive heating, microwave oven, etc.

V_{CE}	1350	V
I_C	25	A
$V_{CE(SAT)}$ I_C=25A	2.0	V

FEATURES

- High breakdown voltage to 1350V for improved reliability
- Trench-Stop Technology offering :
  - High speed switching
  - High ruggedness, temperature stable
  - Low V_{CEsat}
  - Easy parallel switching capability due to positive temperature coefficient in V_{CEsat}
- Soft current turn-off waveforms
- Enhanced avalanche capability





APPLICATION

- Inductive cooking
- Inverterized microwave ovens
- Resonant converters
- Soft switching applications

Maximum Ratings

Parameter	Symbol	Value	Unit
Collector-Emitter Breakdown Voltage	V_{CE}	1350	V
DC collector current, limited by T_{jmax} T_C = 25°C T_C = 100°C	I_C	50 25	A
Diode Forward current, limited by T_{jmax} T_C = 25°C T_C = 100°C	I_F	50 25	A
Pulsed collector current, t_p limited by T_{jmax}	I_{Cpuls}	75	A
Turn off safe operating area V_{CE} ≤1350V, T_j ≤ 150°C	-	75	A
Operating junction temperature T_j	-	-40...+150	°C
Storage temperature	T_s	-55...+150	°C
Soldering temperature, wave soldering 1.6mm (0.063in.) from case for 10s	-	260	°C

Thermal Resistance

Parameter	Symbol	Max. Value	Unit
IGBT thermal resistance, junction - case	R_{θ}(j-c)	0.48	K/W
Diode thermal resistance, junction - case	R_{θ}(j-c)	1.2	K/W
Thermal resistance, junction - ambient	R_{θ}(j-a)	40	K/W

Electrical Characteristics of the IGBT（T_j= 25℃ unless otherwise specified）：

Parameter	Symbol	Conditions	Min	Typ	Max	Unit
Static						
Collector-Emitter breakdown voltage	BV_{CES}	V_{GE}=0V , I_C=1mA	1350	1450	-	V
		V_{GE}=0V , I_C=10mA	1350	1450	-	V
Gate threshold voltage	$V_{GE(th)}$	V_{GE}=V_{CE}, I_C=250μA	5.1	5.8	6.4	V
Collector-Emitter Saturation voltage	$V_{CE(sat)}$	V_{GE}=15V, I_C=25A T_j = 25°C T_j = 150°C	 - -	 2.0 2.5	 2.5 -	V
Zero gate voltage collector current	I_{CES}	V_{CE} = 1350V, V_{GE} = 0V T_j = 25°C T_j = 150°C	 - -	 <1 -	 100 1000	μA
Gate-emitter leakage current	I_{GES}	V_{CE} = 0V, V_{GE} = 20V	-	-	100	nA

Parameter	Symbol	Conditions	Min	Typ	Max	Unit
Dynamic						
Input capacitance	C_{ies}	V_{CE} = 25V, V_{GE} = 0V, f = 1MHz	-	2500	-	pF
Output capacitance	C_{oes}		-	70	-	
Reverse transfer capacitance	C_{res}		-	50	-	
Gate charge	Q_G	V_{CC} = 600V, I_C = 25A, V_{GE} = 15V	-	125	-	nC

Switching Characteristic, Inductive Load

Parameter	Symbol	Conditions	Min	Typ	Max	Unit
Dynamic , at T_j = 25° C						
Turn-off delay time	$td_{(off)}$	V_{CC} = 600V, I_C = 25A, V_{GE} = 0/15V, R_g=10Ω	-	180	-	ns
Fall time	t_f		-	40	-	ns
Turn-off energy	E_{off}		-	0.32	-	mJ
Dynamic , at T_j = 150° C						
Turn-off delay time	$td_{(off)}$	V_{CC} = 600V, I_C = 25A, V_{GE} = 0/15V, R_g=10Ω	-	220	-	ns
Fall time	t_f		-	90	-	ns
Turn-off energy	E_{off}		-	0.65	-	mJ

Electrical Characteristics of the DIODE (T_j= 25℃ unless otherwise specified)

Parameter	Symbol	Conditions	Min	Typ	Max	Unit
Dynamic						
Diode Forward Voltage	V_{FM}	I_F = 25A	-	2.3	-	V
Reverse Recovery Time	T_{rr}	I_F= 25A, di/dt= 200A/μs	-	460	-	ns
Reverse Recovery Current	I_{rr}		-	17	-	A
Reverse Recovery Charge	Q_{rr}		-	3600	-	nC

Fig. 1 FBSOA characteristics




Fig. 2 Load Current vs. Frequency




Fig. 3 Output characteristics




Fig. 4 Saturation voltage characteristics




Fig. 5 Turn-off time vs. gate resistor




Fig. 6 Turn-off time vs. collector current




Fig. 7 Switching loss vs. gate resistor




Fig. 8 Switching loss vs. collector current




Fig. 9 Gate charge characteristics






Fig. 10 Capacitance characteristics



PG-TO247-3



DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	4.83	5.21	0.190	0.205
A1	2.27	2.54	0.089	0.100
A2	1.85	2.16	0.073	0.085
b	1.07	1.33	0.042	0.052
b1	1.90	2.41	0.075	0.095
b2	1.90	2.16	0.075	0.085
b3	2.87	3.38	0.113	0.133
b4	2.87	3.13	0.113	0.123
c	0.55	0.68	0.022	0.027
D	20.80	21.10	0.819	0.831
D1	16.25	17.65	0.640	0.695
D2	0.95	1.35	0.037	0.053
E	15.70	16.13	0.618	0.635
E1	13.10	14.15	0.516	0.557
E2	3.68	5.10	0.145	0.201
E3	1.00	2.60	0.039	0.102
e	5.44 (BSC)		0.214 (BSC)	
N	3		3	
L	19.80	20.32	0.780	0.800
L1	4.10	4.47	0.161	0.176
øP	3.50	3.70	0.138	0.146
Q	5.49	6.00	0.216	0.236
S	6.04	6.30	0.238	0.248