


REVISIONS				
REV	NUMBER	DESCRIPTION	DWN	CHK
A		DESIGN	James	9/26

200±2



NOTES:

- ELECTRICAL:
 - VOLTAGE RATING:DCV 300V 10MS
 - CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
 - INSULATION RESISTANCE: 5.0M OHM/MIN.
 - THE CABLE SHOULD BE 100% ELECTRICAL TEST
 - IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
- MATERIAL:
 - SEE TABLE
- ALL COMPONENTS ARE RoHS COMPLIANT.

深圳市金航标电子有限公司

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
④	端子	国产 I-PEX 1.13端子, 镀金	1
③	套管	OD:4.5* 35 mm 白色热缩套管	1
②	铜管	铜管: 5.2*24mm, 1.13线用	1
①	同轴线	RF1.13白色同轴线, OD:1.13mm	AS
ALL DIMENSION ARE IN MM			
DRAWN		JAMES	DATE 2026-08-16
CHKD.		FRANK	2026-08-16
APPD.		SCOTT	2026-08-16
COMPUTER GENERATED N SOLIDWORKS DO NOT SCALE THIS DRAWING			
PROJECTION			
GENERAL TOLERANCE FOR ANGLES X.X XXX X.XXX ±1° ±0.3 ±0.25 ±0.150			
TITLE		KH1NB(2.4G)W200-03-A.3	
SIZE		铜管天线	
SCALE:Free		DWG Number:	
TYPE		REV	

CUSTOMER P.I.N: