



SPECIFICATION:

1.MATERIAL:

1.1 HOUSING: LCP E130i 30% G/F UL 94V-0

1.2 COLOR: BLACK

1.3 CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm

1.4 PEG: BRASS C2680R-H,T=0.20mm

2.FINISH:








2.1 CONTACT:1u"/3u"/5u"/15u"GOLD PLATING ON CONTACT AREA

2.2 100u" TIN PLATING ON SOLDER TAILS

2.3 30u" NICKEL UNDERPLATING OVER ALL

2.4 PEG:100u" TIN PLATING ON SOLDER TAILS

2.5 30u" NICKEL UNDERPLATING OVER ALL

RECOMMENDED PCB LAYOUT
UNLESS
TOLERANCE: +/ -0.05

环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680		Tin/Ni Plated
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK

UNLESS OTHERWISE
SPECIFIED TOLERANCESDECIMALS: ANGLES:
X :±0.30 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	SATA 7+15P 直立式SMT 带接地片 加盖子			
DWN	xiong	PART NO. SATA-035F-22PS1BY		
CHKD	lee	SCALE:1:1	UNIT: mm	⊙
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4

CUSTOMER COPY