


Description:

This N-Channel MOSFET uses advanced trench technology and design to provide excellent $R_{DS(on)}$ with low gate charge.

It can be used in a wide variety of applications.

Features:

- 1) $V_{DS}=30V, I_D=30A, R_{DS(on)} < 10m\Omega @ V_{GS}=10V$ (Typ: $11m\Omega$)
- 2) Low gate charge.
- 3) Green device available.
- 4) Advanced high cell density trench technology for ultra low $R_{DS(on)}$.
- 5) Excellent package for good heat dissipation.
- 6) MSL3



Package Marking and Ordering Information:

Part NO.	Marking	Package	Packing
DOZ40N03	40N03	DFN3*3-8	5000 pcs/Reel

Absolute Maximum Ratings: ($T_C=25^\circ\text{C}$ unless otherwise noted)

Symbol	Parameter	Ratings	Units
V_{DS}	Drain-Source Voltage	30	V
V_{GS}	Gate-Source Voltage	± 20	V
I_D	Continuous Drain Current Continuous ($T_C=25^\circ\text{C}$) ¹	30	A
	Continuous Drain Current-($T_C=100^\circ\text{C}$) ¹	21	
I_{DM}	Drain Current – Pulsed ²	120	A
E_{AS}	Single Pulse Avalanche Energy ³	24.2	mJ
P_D	Power Dissipation ($T_C=25^\circ\text{C}$)	15.6	W
T_J, T_{STG}	Operating and Storage Junction Temperature Range	-55 to +150	$^\circ\text{C}$

Thermal Characteristics:

Symbol	Parameter	Max	Units
$R_{\theta JC}$	Thermal Resistance, Junction to Case	8	$^\circ\text{C}/\text{W}$
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	62	$^\circ\text{C}/\text{W}$

Electrical Characteristics: ($T_C=25^{\circ}\text{C}$ unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Units
Off Characteristics						
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V, I _D =250 μ A	30	---	---	V
I _{DSS}	Drain-Source Leakage Current	V _{GS} =0V, V _{DS} =30V, T _J =25℃	---	---	1	μ A
I _{GSS}	Gate-Source Leakage Current	V _{GS} =± 20V, V _{DS} =0A	---	---	± 100	nA
On Characteristics						
V _{GS(th)}	Gate-Source Threshold Voltage	V _{GS} =V _{DS} , I _D =250 μ A	1	---	2.5	V
R _{DS(ON)}	Drain-Source On Resistance ⁴	V _{GS} =10V, I _D = 15A	---	7.1	10	m Ω
		V _{GS} =4.5V, I _D = 10A	---	11	17	
G _{FS}	Forward Transconductance	V _{DS} =5V, I _D =15A	---	24.4	---	S
Dynamic Characteristics						
C _{iss}	Input Capacitance	V _{DS} =15V, V _{GS} =0V, f=1MHz	---	800	---	pF
C _{oss}	Output Capacitance		---	126	---	
C _{rss}	Reverse Transfer Capacitance		---	108	---	
Switching Characteristics						
t _{d(on)}	Turn-On Delay Time	V _{DD} =15V , V _{GS} =10V , R _G =3 Ω , I _D =10A	---	6.4	---	ns
t _r	Rise Time		---	5	---	ns
t _{d(off)}	Turn-Off Delay Time		---	25	---	ns
t _f	Fall Time		---	7	---	ns
Q _g	Total Gate Charge	V _{DS} =15V , V _{GS} =4.5V , I _D =20	---	9.82	---	nC
Q _{gs}	Gate-Source Charge		---	6.54	---	nC
Q _{gd}	Gate-Drain “Miller” Charge		---	4.54	---	nC
Drain-Source Diode Characteristics						
I _S	Contiuos Source Curent	V _D =V _G =0V	---	---	25	A
I _{SM}	Pulsed Source Curent		---	---	100	A
V _{SD}	Source-Drain Diode Forward Voltage	V _{GS} =0V , I _S =40A	---	---	1.2	V
t _{rr}	Reverse Recovery Time	I _F =20A , di/dt=100A/μs	---	7	---	ns
Q _{rr}	Reverse Recovery Charge		---	6.3	---	nC

Notes:

1. Computed continuous current assumes the condition of $T_{j,Max}$ while the actual continuous current depends on the thermal & electro-mechanical application board design
2. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature
3. EAS condition : $T_J=25^{\circ}C, V_{DD}=15V, V_G=10V, L=0.5mH$
4. Pulse Test: Pulse Width $\leq 300\mu s$, Duty Cycle $\leq 0.5\%$

Typical Characteristics: ($T_C=25^{\circ}C$ unless otherwise noted)




Figure 1: Output Characteristics




Figure 2: Typical Transfer Characteristics




Figure 3: On-resistance vs. Drain Current




Figure 4: Body Diode Characteristics




Figure 5: Gate Charge Characteristics




Figure 6: Capacitance Characteristics




Figure 7: Normalized Breakdown Voltage vs. Junction Temperature




Figure 8: Normalized on Resistance vs. Junction Temperature




Figure 9: Maximum Safe Operating Area






Figure.10: Maximum Effective Transient Thermal Impedance, Junction-to-Case

DFN3X3-8 Package Outline Data



**Land Pattern
(Only for Reference)**




UNIT: mm

SYMBOL	DIMENSIONAL REQMTS		
	MIN	NOM	MAX
A	0.70	0.75	0.80
b	0.25	0.30	0.35
c	0.10	0.15	0.25
D	3.25	3.35	3.45
D1	3.00	3.10	3.20
D2	1.78	1.88	1.98
D3	---	0.13	---
E	3.20	3.30	3.40
E1	3.00	3.15	3.20
E2	2.39	2.49	2.59
e	0.65BSC		
H	0.30	0.39	0.50
L	0.30	0.40	0.50
L1	---	0.13	---
θ	---	10°	12°
M	*	*	0.15


* Not specified

Tape & Reel Information

Dimensions in mm



Symbol	A0	B0	K0	D0	D1	P0	P1	10*P0
Spec	3.55 $\pm$ 0.10	3.45 $\pm$ 0.10	1.13 $\pm$ 0.10	1.55 $\pm$ 0.10	1.55 $\pm$ 0.10	4.00 $\pm$ 0.10	8.00 $\pm$ 0.10	40.0 $\pm$ 0.10
Symbol	W	E	F	P2	t			
Spec	12.00 $\pm$ 0.10	1.75 $\pm$ 0.10	5.50 $\pm$ 0.10	2.00 $\pm$ 0.10	0.20 $\pm$ 0.05			



Pulling direction →

Marking Information:


①. Part NO.

②. Date Code(YWWG / R)

Y : Year Code , last digit of the year

WW : Week Code(01-53)

G/R : G(Green) /R(Lead Free)



Previous Version

Version	Date	Subjects (major changes since last revision)
2.0	2025-09-10	Release of final version

Attention :

- Information furnished in this document is believed to be accurate and reliable. However, Shenzhen Doingter Semiconductor Co.,Ltd. assumes noresponsibility for the consequences of use without consideration for such information nor use beyond it.
 - Information mentioned in this document is subject to change without notice, apart from that when an agreement is signed, Shenzhen Doingter complies with the agreement. Products and information provided in this document have no infringement of patents.
 - Shenzhen Doingter assumes noresponsibility for any infringement of other rights of third parties which may result from the use of such products and information. This document supersedes and replaces all information previously supplied.
-  Is a registered trademark of Shenzhen Doingter Semiconductor Co., Ltd. Copyright © 2013 Shenzhen DoingterSemiconductor Co.,Ltd. Printed All rights reserved.