






RoHS Compliant



High photosynthesis 台高(H)	The female seat neight 插座高度(H1)	The male seat neight 公座高度(H2)	Insertion height (H3)
4.0	3.0	1.0	1.9
4.5	3.5	1.0	1.9
5.0	3.0/4.0	2.0/1.0	1.9
5.5	3.5/4.5	2.0/1.0	1.9
6.0	4.0	2.0	1.9
6.5	4.5	2.0	1.9
7.0	3.0	4.0	1.9
7.5	3.5	4.0	1.9
8.0	4.0	4.0	1.9
8.5	4.5	4.0	1.9



技术指标:

- 1.塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
- 2.温度范围: -40°C~85°C.
- 3.额定电压: 125V, AC.
- 4.接触电阻: $\leq 0.02\Omega$.
- 5.绝缘电阻: $\geq 100M\Omega$

序号	品名	材质
①	0.8 Pitch双槽立式 BTB公座胶芯	PA10T UL94 V-0, 颜色:黑色
②	0.8 Pitch双槽立式 BTB公座端子	铜合金/表面点镀金
③	0.8 Pitch双槽立式 BTB公座吸盖	LCP UL94 V-0, 颜色:黑色

Part No	CKT	A	B	C	D	E
LCK-BTG0820-8PSLYR-GO	8	2.40	3.45	5.10	4.20	4.00
LCK-BTG0820-10PSLYR-GO	10	3.20	4.25	5.90	5.00	
LCK-BTG0820-12PSLYR-GO	12	4.00	5.05	6.70	5.80	
LCK-BTG0820-14PSLYR-GO	14	4.80	5.85	7.50	6.60	
LCK-BTG0820-16PSLYR-GO	16	5.60	6.65	8.30	7.40	
LCK-BTG0820-18PSLYR-GO	18	6.40	7.45	9.10	8.20	
LCK-BTG0820-20PSLYR-GO	20	7.20	8.25	9.90	9.00	
LCK-BTG0820-22PSLYR-GO	22	8.00	9.05	10.70	9.80	
LCK-BTG0820-24PSLYR-GO	24	8.80	9.85	11.50	10.60	8.00
LCK-BTG0820-26PSLYR-GO	26	9.60	10.65	12.30	11.40	
LCK-BTG0820-28PSLYR-GO	28	10.40	11.45	13.10	12.20	
LCK-BTG0820-30PSLYR-GO	30	11.20	12.25	13.90	13.00	
LCK-BTG0820-32PSLYR-GO	32	12.00	13.05	14.70	13.80	
LCK-BTG0820-34PSLYR-GO	34	12.80	13.85	15.50	14.60	
LCK-BTG0820-36PSLYR-GO	36	13.6	14.65	16.30	15.40	
LCK-BTG0820-38PSLYR-GO	38	14.40	15.45	17.10	16.20	
LCK-BTG0820-40PSLYR-GO	40	15.20	16.25	17.90	17.00	
LCK-BTG0820-44PSLYR-GO	44	16.80	17.85	19.50	18.60	
LCK-BTG0820-50PSLYR-GO	50	19.20	20.25	21.90	21.00	
LCK-BTG0820-60PSLYR-GO	60	23.20	24.25	25.90	25.00	
LCK-BTG0820-70PSLYR-GO	70	27.20	28.25	29.90	29.00	
LCK-BTG0820-80PSLYR-GO	80	31.20	32.25	33.90	33.00	
LCK-BTG0820-100PSLYR-GO	100	39.20	40.25	41.90	41.00	

MEASURE POINT:
QUADRANT POINT (QP)
TANGENCY POINT (TP)
INTERSECTION POINT (IP)

UNLESS OTHERWISE
SPECIFIED,TOLERANCE:
X. ±0.25
X.x ±0.20
X.xx ±0.15
ANGULAR ±3°

联晟欣连接器(深圳)有限公司
Lianshengxin Connector (Shenzhen) Co., Ltd

DESIGN Andy DATE 2014.12.24 TITLE:
CHECKED DATE
APPROVED DATE
PART NO: LCK-BTG0820-XXPSLYR-GO REV: 04 SCALE: 1:1 UNIT: mm
DRAWING NO: 102022802 SIZE: A4 SHEET: 1/1

