



RoHS

REV	ECN NO.	DESRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2024.05.24









SPECIFICATIONS
1. Current rating: 2A
2. Temperature range: -40°C ~ +105°C
3. Insulation resistance: 1000MΩ Min.
4. Withstanding voltage: 500V AC/ minute.
5. Contact resistance: 20mΩ Max.

Material:
Insulator Material:PA6T (UL 94V-0)
Contact Material:Brass
Plating:Matte Tin or gold plated over Nickel
Mate with XFCN PZ200 Double Row series

Ordering Code:

PM200V-12-XX-H43
1 2

1.序列号
2.Pin位数: 2x2=04P
2x10=20P
2x20=40P

No.of PIN/ROW	Dimension A	B
2*02	4.50	2.00
2*03	6.50	4.00
2*04	8.50	6.00
2*05	10.50	8.00
2*06	12.50	10.00
2*07	14.50	12.00
2*08	16.50	14.00
2*09	18.50	16.00
2*10	20.50	18.00
2*11	22.50	20.00
2*12	24.50	22.00
2*13	26.50	24.00
2*14	28.50	26.00
2*15	30.50	28.00
2*16	32.50	30.00
2*17	34.50	32.00
2*18	36.50	34.00
2*19	38.50	36.00
2*20	40.50	38.00
2*21	42.50	40.00
2*22	44.50	42.00
2*23	46.50	44.00
2*24	48.50	46.00
2*25	50.50	48.00
2*26	52.50	50.00
2*27	54.50	52.00
2*28	56.50	54.00
2*29	58.50	56.00
2*30	60.50	58.00
2*31	62.50	60.00
2*32	64.50	62.00
2*33	66.50	64.00
2*34	68.50	66.00
2*35	70.50	68.00
2*36	72.50	70.00
2*37	74.50	72.00
2*38	76.50	74.00
2*39	78.50	76.00
2*40	80.50	78.00

X.±0.50	X.°±
.X±0.25	.X°±
.XX±0.15	.XX°±
.XXX±0.10	.XXX°±
UNITS:	mm

PART NO: PM200V-12-XX-H43

TITLE: 2.00mm Female Header Connectors

XFCN兴飞连接器

0769-82001899

www.xfconn.com

DWG NO:

APPD	Chen ZhiQiang			
CHKD	Liu Wei	VIEW		
DRAW	Chen HongJiang	SCALE	SHEET	REV
DATE	2024.06.03	NONE	1/1	A1

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED,COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN