

Features

- Very low forward voltage

Ordering Information

- Shipping Qty:8000/7inch Tape& Reel

Mechanical Data

- Case: DFN1608-2
- Molding compound: UL flammability classification rating 94V-0
- Terminals: Tin-plated; solderability per MIL-STD-202, Method 208



DFN1608-2L

PIN	DESCRIPTION
1	Cathode
2	Anode



Marking:T2A4

Absolute Maximum Ratings (T_A=25°C unless otherwise noted)

Parameter	Symbol	Value	Unit
DC Reverse Voltage	V _R	40	V
Maximum Average Forward Output Current	I _{F(AV)}	2	A
Peak Forward Surge Current (8.3ms single half sine-wave)	I _{FSM}	30	A

Thermal Characteristics

Parameter	Symbol	Value	Unit
Thermal Resistance Junction to Ambient (Typ)	P _D	80	°C/W
Operating Junction Temperature	T _J	-55 ~ +125	°C
Storage Temperature Range	T _{STG}	-55 ~ +150	°C

Electrical Characteristics (T = 25°C unless otherwise noted)

Parameter	Symbol	Test Condition	Min.	Typ.	Max.	Unit
Reverse Breakdown Voltage	$V_{(BR)R}$	$I_R = 100\mu A$	40	-	-	V
Forward Voltage	V_F	$I_F = 1A$	-	-	0.47	V
		$I_F = 2A$	-	-	0.55	V
Maximum Peak Reverse Current	I_R	$V_R = 40V$	-	-	15	μA

Typical Electrical Characteristic Curves

FIG1: I_o -TL Curve




FIG2: Surge Forward Current Capability




FIG3: Typical Reverse Characteristics







FIG4: Typical Forward Characteristics




Outline Drawing Package information

DFN1608-2



DFN1608-2			
DIM	MIN	NOR	MAX
A	0.32	0.37	0.42
A1	0.01	0.03	0.05
b	0.65	0.70	0.75
b1	0.25	0.30	0.35
D	1.55	1.60	1.65
E	0.75	0.80	0.85
k	0.35	0.40	0.45
L	0.30	0.35	0.40
L1	0.70	0.75	0.80
A3	0.127REF.		
All Dimensions in mm			

SOLDERING FOOTPRINT



DFN1608-2	
DIM	(mm)
X1	1.05
X2	0.65
L	1.90
Y	0.80
K	0.20