

RoHS

REV	ECN NO.	DESRPTION	DESIGN	APPROVAL	DATE
A1	NEW	新版发行			2026.07.07

SPECIFICATIONS

1. Current rating: 1A AC, DC
- 2.Voltage rating: 50V AC, DC
3. Temperature range: -40°C ~ +105°C
4. Insulation resistance: 100MQ Min.
5. Withstanding voltage: 200V AC/ minute.6
- . Contact resistance: 20mΩ Max.

Material:

Insulator: LCP UL 94V-0

Contact: Brass

Solder Tab: Brass

Plating: Matte Tin or gold plated over Nickel

Circuits: 02~16P

Mate with:XFCN P1010 series Housing

Ordering Code:

M1010VS-XXP-001






1 2

1.序列号

2. Pin位数 02-16P

No.of PIN/ROW	Dimension		
	A	B	C
02	4.30	1.00	3.25
03	5.30	2.00	4.25
04	6.30	3.00	5.25
05	7.30	4.00	6.25
06	8.30	5.00	7.25
07	9.30	6.00	8.25
08	10.30	7.00	9.25
09	11.30	8.00	10.25
10	12.30	9.00	11.25
11	13.30	10.00	12.25
12	14.30	11.00	13.25
13	15.30	12.00	14.25
14	16.30	13.00	15.25
15	17.30	14.00	16.25
16	18.30	15.00	17.25

X.±0.50	X.°±	PART NO: M1010VS-XXP-001		XFCN 兴飞连接器			
.X±0.25	.X°±						
.XX±0.15	.XX°±	TITLE: 1.00mm Crimp Style Connectors		0769-82001899			
.XXX±0.10	.XXX°±			www.xfconn.com			
UNITS:	mm			DWG NO:			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN		APPD	Chen ZhiQiang	VIEW			
		CHKD	Liu Wei				
		DRAW	Chen HongJiang	SCALE	SHEET	REV	
		DATE	2026.07.07	NONE	1/1	A1	



RECOMMENDER P.C.B.LAYOUT TOP VIEW
(COMPONENT SIDE TOLERANCE±0.1)