珠海市大鹏电子科技有限公司

Specification

产品规格书

客户名称 (CUSTOMER):	
样品名称 (DESCRIPTION):	直插光耦
型号 (Part No):	DP-817
日期 (Date):	2026-07-16

公司邮箱：josensong@163.com
销售热线：15914189777


生产部 Production Dept.	品质部 Quality Dept.	工程部 Engineering Dept.	市场部 Marketing Dept.
客户承认结果 Customer acknowledges Results	客户签名确认 Customer signature confirmation	批　准 Approval	制　定 Formulate

珠海市大鹏电子科技有限公司


● Features:

- Current transfer ratio (CTR: 50~600% at I_F =5mA, V_{CE} =5V)
- High isolation voltage between input and output (Viso=4500 V rms)
- Creepage distance >7.62 mm
- Operating temperature up to +110°C
- Compact small outline package
- Pb free and RoHS compliant.


● Dimensions



Schematic



Pin Configuration
1. Anode
2. Cathode
3. Emitter
4. Collector



● Description

1. The DP-817 series are optically coupled isolators containing a GaAs light emitting diode and an NPN silicon phototransistor
2. The lead pitch is 2.54mm

● Applications:

1.Computer terminals.
2.System appliances, measuring instruments.
3.Registers, copiers, automatic vending machines.
4.Electric home appliances, such as fan heaters, etc. of different potentials and impedances.
5.Signal transmission between circuits

●Absolute Maximum Ratings (Ta=25℃)

Parameter		Symbol	Rating	Unit
INPUT	Forward Current	I_F	50	mA
	Reverse Voltage	V_R	6	V
	Power Dissipation	P	70	mW
OUTPUT	Collector-Emitter Voltage	V_{CEO}	35	V
	Emitter- Collector Voltage	V_{ECO}	6	
	Collector Current	I_C	50	mA
	Collector Power Dissipation	P_C	150	mW
Total Power Dissipation		P_{tot}	200	mW
*1 Isolation Voltage		V_{iso}	4,500	Vrms
Rated impulse isolation voltage		V_{IOTM}	5,000	V
Rated repetitive peak isolation voltage		V_{IORM}	630	V
Operating Temperature		T_{opr}	-40 to + 85	℃
Storage Temperature		T_{stg}	-55 to + 125	
*2 Soldering Temperature		Tsol	260	

*1. AC For minute, R.H. =40~60%
Isolation voltage shall be measured using the following method.
(1) Short between anode and cathode on the primary side and between collector and emitter on the secondary side.
(2) The isolation voltage tester with zero-cross circuit shall be used.
(3) The waveform of applied voltage shall be a sine wave.

*2. For 10 Seconds

●Electro-Optical Characteristics (Ta=25℃)

Parameter		Symbol	Conditions	MIN.	TYP.	MAX.	Unit.
INPUT	Forward Voltage	V_F	I_F=20mA	---	1.2	1.4	V
	Reverse Current	I_R	V_R=4V	---	---	10	μA
	Terminal Capacitance	C_t	V=0, f=1KHz	---	30	250	pF
OUTPUT	Collector Dark Current	I_{CEO}	V_{CE}=20V, I_F=0	---	---	100	nA
	Collector-Emitter Breakdown Voltage	BV_{CEO}	I_C=0.1mA I_F=0	80	---	---	V
	Emitter-Collector Breakdown Voltage	BV_{ECO}	I_E=10μA I_F=0	6	---	---	V
TRANSFER CHARACTERISTICS	Collector Current	I_c	I_F=5mA	2.5	---	30	mA
	*1 Current Transfer Ratio	CTR	V_{CE}=5V	50	---	600	%
	Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	I_F=20mA I_C= 1mA	---	0.1	0.2	V
	Isolation Resistance	R_{iso}	DC500V 40~60%R.H.	5×10^{10}	1×10^{11}	---	Ω
	Floating Capacitance	C_f	V=0, f=1MHz	---	0.6	1	pF
	Cut-Off Frequency	f_c	V_{CE}=5V, I_C=2mA R_L=100Ω, -3dB	---	80	---	kHz
	Response Time(Rise)	t_r	V_{CE}=2V, I_C=2mA R_L=100Ω	---	4	18	μs
	Response Time(Fall)	t_f		---	3	18	μs

*1 CTR= I_C / I_F × 100%

●RANK TABLE OF CURRENT TRANSFER RATIO(CTR)

RANK MARK.	Min. (%)	Max. (%)
L	50	100
A	80	160
B	130	260
C	200	400
D	300	600
L or A or B or C or D	50	600

Notes:

1. Conditions: I_F=5mA, V_{CE}=5V, Ta=25℃.

● CHARACTERISTICS CURVES

Fig.1 Forword Current vs. Ambient Temperatute




Fig.2 Collector Power Dissiption vs. Ambient Temperature




Fig.3 Collector-emitter Saturation Voltage vs. Forward Current




Fig.4 Forward Current vs. Forward Voltage




Fig.5 Current Transfer Ratio vs. Forward Current





Fig.6 Collector Current vs. Collector-emitter Voltage



●Characteristics Curves

Fig.7 Relative Current Transfer Ratio vs. Ambient Temperature




Fig.8 Collector-emitter Saturation Voltage vs. Ambient Temperature




Fig.9 Collector Dark Current vs. Ambient Temperature




Fig.10 Response Time vs. Load Resistance







Fig.11 Frequency Response



Test Circuit for Response Time



Test Circuit for Frequency Response



● Reliability Test

Classification	Test Item	Reference Standard	Test Conditions	Result
Endurance Test	Operation Life	MIL-STD-750:1026 MIL-STD-883:1005 JIS C 7021 :B-1	Connect with a power If=50mA Ta=Under room temperature Test time=1,000hrs	0/20
	High Temperature High Humidity Reverse Bias (H3TRB)	JIS C 7021 :B-11	Ta=+85℃±5℃, RH=85% PTR=V_{CE} absolute max rating*80% Test time=1000hrs	0/20
	High Temperature Reverse Bias (HTRB)	JIS C 7021 :B- 8	Ta=+105℃±5℃ PTR=V_{CE} absolute max rating Test time=1000hrs	0/20
	High Temperature Storage	MIL-STD-883:1008 JIS C 7021 :B-10	High Ta=+125℃±5℃ Test time=1,000hrs	0/20
	Low Temperature Storage	JIS-C-7021 :B-12	Low Ta=-55℃±5℃ Test time=1,000hrs	0/20
	Autoclave	JESD 22-A102-B	P=15PSIG, Ta=121℃ Humi. =100%RH, 48hrs	0/20
Environmental Test	Temperature Cycling	MIL-STD-202:107D MIL-STD-750:1051 MIL-STD-883:1010 JIS C 7021 :A-4	125℃ ~ 25℃ ~ -55℃ ~ 25℃ 30min 5min 30min 5min Test Time=20cycle	0/20
	Thermal Shock	MIL-STD-202:107D MIL-STD-750:1051 MIL-STD-883:1011	125℃ ~-55℃ 20min 20min Test Time=20cycle	0/20
	Solder Resistance	MIL-STD-202:201A MIL-STD-750:2031 JIS C 7021 :A-1	Operation heating : 300℃, within 10±1seconds.	0/20
	Solder Ability	MIL-S-883:2003 JIS C 7021 :A-2	Operation heating : 260℃, within 5±1seconds.	0/20

●Judgment Criteria Of Failure For The Reliability

Symbol	Measuring conditions	Judgment criteria for failure
V_F (V)	If=20mA	Over Ux1.0
Ir(uA)	Vr=4V	Over Ux1.0
CTR(%)	If=5mA, V_{CE}=5V	Shift>1.2
$V_{CE(sat)}$	I_F=20mA, I_C= 1mA	Over Ux1.0
BV_{CEO}	I_C=0.1mA, I_F=0	Over Lx1.0
BV_{ECO}	I_E=10μA, I_F=0	Over Lx1.0