

Features


- Zero Forward/Reverse Recovery Current
- High Blocking Voltage
- High Frequency Operation
- Positive Temperature Coefficient on V_F
- Temperature Independent Switching Behavior
- High surge current capability
- 100% avalanche tested

Benefits

- Higher System Efficiency
- Parallel Device Convenience without thermal runaway
- High Temperature Application
- No Switching loss
- Hard Switching & Higher Reliability
- Environmental Protection

Applications

- Servo Drives
- Solar / Wind Inverters
- AC/DC converters
- DC/DC converters
- Uninterruptable power supplies



TO-220-2



Maximum Ratings ($T_C=25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	Test conditions	Value	Unit
Peak Repetitive Reverse Voltage	V_{RRM}		650	V
Peak Reverse Surge Voltage	V_{RSM}		650	V
DC Blocking Voltage	V_R		650	V
Continuous Forward Current	I_F	$T_C=25^{\circ}\text{C}$ $T_C=135^{\circ}\text{C}$ $T_C=148^{\circ}\text{C}$	58 25 20	A
Non repetitive Forward Surge Current	I_{FSM}	$T_C = 25^{\circ}\text{C}$, $t_p=10$ ms, Half Sine Pulse $T_C = 110^{\circ}\text{C}$, $t_p=10$ ms, Half Sine Pulse	120 110	A
Repetitive peak Forward Surge Current	I_{FRM}	$T_C = 25^{\circ}\text{C}$, $t_p=10$ ms, Freq = 0.1Hz, 100 cycles, Half Sine Pulse $T_C = 110^{\circ}\text{C}$, $t_p=10$ ms, Freq = 0.1Hz, 100 cycles, Half Sine Pulse	110 100	A
Total power dissipation	P_D	$T_C=25^{\circ}\text{C}$	176	W
Operating Junction Temperature	T_J		-55 to 175	$^{\circ}\text{C}$
Storage Temperature	T_{STG}		-55 to 175	$^{\circ}\text{C}$

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

Electrical Characteristics

Parameter	Symbol	Test conditions	Min	Typ	Max	Unit
DC Blocking Voltage	V_{DC}	$I_R = 250\mu A, T_J = 25^\circ C$	650			V
Forward Voltage	V_F	$I_F = 20A, T_J = 25^\circ C$		1.5	1.8	V
		$I_F = 20A, T_J = 125^\circ C$		1.6		V
		$I_F = 20A, T_J = 175^\circ C$		1.7		V
Reverse Current	I_R	$V_R = 650V, T_J = 25^\circ C$		20	80	μA
		$V_R = 650V, T_J = 125^\circ C$		120		μA
		$V_R = 650V, T_J = 175^\circ C$		250		μA
Total Capacitive Charge	Q_C	$V_R = 400V, T_J = 25^\circ C$		44		nC
Total Capacitance	C	$V_R = 1V, T_J = 25^\circ C,$ Freq = 1MHz		770		pF
		$V_R = 200V, T_J = 25^\circ C,$ Freq = 1MHz		90		
		$V_R = 400V, T_J = 25^\circ C,$ Freq = 1MHz		64		

Note: This is a majority carrier diode, so there is no reverse recovery charge

Thermal Characteristics

Parameter	Symbol	Condition	Min	Typ	Max	Unit
Thermal Resistance	$R_{th(j-c)}$	junction-case		0.85		$^\circ C/W$

Ordering Information

Order number	Package	Marking	Operation Temperature Range	MSL Grade	Ship,Quantity	Green
SC3D20065A-JSM	TO-220-2	SC3D20065A	-55 to 175 $^\circ C$	1	TUBE,1000	RoHS

Typical Electrical Curves

Figure 1. Forward Characteristics




Figure 2. Forward Characteristics




Figure 3. Reverse Characteristics




Figure 4. Power Derating




Figure 5. Capacitance vs Reverse Voltage






Figure 6. Recovery Charge vs Reverse Voltage



Package Dimensions

(TO-220-2 Package)



DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	4.30	4.50	0.169	0.177
A1	1.17	1.37	0.046	0.054
A2	2.30	2.50	0.091	0.098
b	0.65	0.85	0.026	0.033
b1	1.19	1.69	0.047	0.066
b2	1.19	1.39	0.047	0.055
c	0.40	0.60	0.016	0.024
D	15.35	15.95	0.604	0.628
D1	9.05	9.45	0.356	0.372
D2	12.30	13.05	0.484	0.514
E	9.80	10.20	0.386	0.402
E1	7.25	8.60	0.285	0.339
e1	5.08		0.200	
N	2		2	
H1	5.90	6.90	0.232	0.272
L	13.00	14.00	0.512	0.551
L1	3.30	3.70	0.130	0.146
øP	3.55	3.90	0.140	0.146
Q	2.60	3.00	0.102	0.118

Revision History

Rev.	Change	Date
V1.0	Initial version	2/23/2022

Important Notice

JSMSEMI Semiconductor (JSMSEMI) PRODUCTS ARE NEITHER DESIGNED NOR INTENDED FOR USE IN MILITARY AND/OR AEROSPACE, AUTOMOTIVE OR MEDICAL DEVICES OR SYSTEMS UNLESS THE SPECIFIC JSMSEMI PRODUCTS ARE SPECIFICALLY DESIGNATED BY JSMSEMI FOR SUCH USE. BUYERS ACKNOWLEDGE AND AGREE THAT ANY SUCH USE OF JSMSEMI PRODUCTS WHICH JSMSEMI HAS NOT DESIGNATED FOR USE IN MILITARY AND/OR AEROSPACE, AUTOMOTIVE OR MEDICAL DEVICES OR SYSTEMS IS SOLELY AT THE BUYER' S RISK.

JSMSEMI assumes no liability for application assistance or customer product design. Customers are responsible for their products and applications using JSMSEMI products.

Resale of JSMSEMI products or services with statements diferent from or beyond the parameters stated by JSMSEMI for that product or service voids all express and any implied warranties for the associated JSMSEMI product or s ervice. JSMSEMI is not responsible or liable for any such statements.

JSMSEMI All Rights Reserved. Information and data in this document are owned by JSMSEMI wholly and may not be edited, reproduced, or redistributed in any way without the express written consent from JSMSEMI.

Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the JSMSEMI product that you intend to use.

For additional information please contact Kevin@jsmsemi.com or visit www.jsmsemi.com