


REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



SPECIFICATION:

1.MATERIAL:

HOUSING: LCP/PA9T COLOR:BLACK

CONTACT:BRASS C2680R-H,T=0.25mm

PEG: BRASS C2680R-H,T=0.30mm

2.FINISH:






CONTACT: 1u"/3u"/5u"/5u" GOLD PLATING ON CONTACT AREA

100u" MIN. TIN PLATING ON SOLDERTAILS

30u" MIN.NICKEL UNDERPLATING OVER ALL

PEG: 100u" MIN. TIN PLATING ON SOLDERTAILS

30u" MIN.NICKEL UNDERPLATING OVER ALL



环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680		Tin/Ni Plated
2	Terminal	Brass C2680		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
.X±0.30	.X°±3°	PART NO.	TITLE: SATA 7P 公座B型	
.XX±0.20	.XX°±2°	JXT-SATA02-GS7P	全开窗鱼叉 侧插式针长2.05mm	
.XXX±0.05	.XXX°±0.5°	DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia	SCALE N:A SHEET 1/1	
MATERILA	— — —	APPD: Ava		
FINISH	— — —			