



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

SPECIFICATION:

1.MATERIAL:

HOUSING:LCP 30% G/F UL 94V-0

COLOR:BLACK

CONTACT:BRASS C2680R-H,T=0.25mm

PEG: BRASS C2680R-H,T=0.30mm

2.FINISH:

CONTACT:1u",3u",5u",15u"GOLD PLATING ON CONTACT AREA
100u" MIN.TIN PLATING ON SOLDERTAILS

40u" MIN.NICKEL UNDERPLATING OVER ALL

3.ELECTRICAL:

CURRENT RATING:1.5 AMPERE PER CONTACT






CONTACT RESISTANCE:30 MILLIOHMS MAX

INSULATION RESISTANCE:1000 MEGOHMS MIN



DIELECTRIC WITH STANDING VOLTAGE:500 VDC

OPERATING TEMPERATURE: -40°C ~ +85°C

4.THE MARK (XX) DIMENSIONS MUST BE MEASURED BY FAI.



SECTION:Y-Y



PCB LAYOUT
TOLERANCES:±0.05MM

环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680		Tin/Ni Plated
2	Terminal	Brass C2680		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
.X±0.30	.X'±3"	PART NO.	TITLE: SATA7+15P公座	
.XX±0.20	.XX'±2"	JXT-SATA08-G22PS	沉板式SMT H0.9 (半包式)	
.XXX±0.05	.XXX'±0.5"	DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia		
MATERILA	---	APPD: Ava		
FINISH	---			
			SCALE	SHEET
			N:A	1/1