








REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



技术指标(Technical Index):

- 1.工作温度(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):250V DC/AC.
- 3.额定电流(Rated current):2.0A DC/AC.
- 4.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 5.耐压值(Dielectricwithstanding voltage):1000V AC/minute.
- 6.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.
- 7.适用线规(Apply to gauge):AWG#24~#28.
- 8.适用基板厚度(Applicable PC board thickness):1.2~1.6mm.



序号	品名	材质
1	端子	Phosphor Bronze Bright tin plated

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
X.±0.50	±1°	PART NO.		TITLE:		
X.X±0.20		B-SAN2.0-2DP2		SAN2.0 WTB直插端子		
X.XX±0.10		DESIGN: Ethan		MANUFACTURE DWG		
UNITS	mm	CHED: Olvia			SCALE	SHEET
MATERILA	— — —	APPD: Ava			N:A	1/1