










REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



RECOMMEND PCB LAYOUT
PCB TOLERANCE:±0.05



SPECIFICATION:

1.MATERIAL:

HOUSING: LCP 30% G/F UL 94V-0
COLOR:BLACK
CONTACT:BRASS C2680R-H,T=0.25mm
PEG: BRASS C2680R-H,T=0.30mm

2.FINISH:

CONTACT: 1u"~15u"GOLD/TIN PLATING ON CONTACT AREA
100u". TIN PLATING ON SOLDERTAILS
50u".NICKEL UNDERPLATING OVER ALL
PEG: 100u". TIN PLATING ON SOLDERTAILS
50u".NICKEL UNDERPLATING OVER ALL

3.SPECIFICATION:

RATING VOLTAGE:12V AC
RATING CURRENT:1.5AMP
CONTACT RESISTANCE:30mΩ MAX
INSULATION RESISTANCE:1000MΩ MIN AT500V DC
WITHSTANDING VOLTAGE:AC 500V FOR 1 MINUTE
MATING FORCE:4.59KGF MAX(45N MAX)
EXTRACTION FORCE:1.02KGF MIN(10N MIN)
DURABILITY:500CYCLES
TEMPERATURE RANGE:-20℃ TO +85℃

环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680		Tin/Ni Plated
2	Terminal	Brass C2680		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
.X±0.30	.X°±3°	PART NO.	TITLE: SATA 7P公座A型全包	
.XX±0.20	.XX°±2°	JXT-SATA01-GS7P	开窗 针长2.05mm 鱼叉侧插式	
.XXX±0.05	.XXX°±0.5°	DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia		
MATERILA	---	APPD: Ava		
FINISH	---			
				SCALE SHEET N:A 1/1