






REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



SPECIFICATION:

MATERIAL:

HOUSING: LCP 30% G/F UL 94V-0

COLOR:BLACK

CONTACT: PHOSPHOR BRONZE C2680 H,T=0.25mm

PEG: BRASS C2680R H,T=0.30mm

SHELL: spcc,T=0.30mm

FINISH:

CONTACT: G/F GOLD/TIN PLATING ON CONTACT AREA

100u" MIN. Matte TIN PLATING ON SOLDER TAILS


50u" MIN. NICKEL UNDERPLATING OVERALL

PEG:100u" MIN. Matte TIN PLATING ON SOLDER TAILS

50u" MIN. NICKEL UNDERPLATING OVERALL

SHELL:100u" MIN. Matte TIN PLATING ON SOLDER TAILS

50u" MIN. NICKEL UNDERPLATING OVERALL



PCB LAYOUT

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.30	.X"±3"	PART NO. JXT-SATA04-GS7P	TITLE: SATA 7P公座及柱AB型带铁壳成品		
.XX±0.20	.XX"±2"				
.XXX±0.05	.XXX"±0.5"	DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia			
MATERILA	— — —	APPD: Ava		SCALE	SHEET
FINISH	— — —			N:A	1/1