

1. MATERIAL:

COLOR:BLACK

CONTACT:PHOSPHOR BRONZE C5191R-H,T=0.25mm

PEG:BRASS C2680R-H, $T=0.30\text{mm}$

2.FINISH:



CONTACT: 1u"/3u"/5u"/15u" GOLD PLATING ON CONTACT AREA


100 μ " TIN PLATING ON SOLDER TAILS

30u" NICKEL UNDERPLATING OVER ALL

PEG:100u" TIN PLATING ON SOLDER TAILS

30u" NICKEL UNDERPLATING OVER ALL



环保要求		产品必须符合ROHS要求			
3	Peg	Brass C2680R-H		Tin/Ni Plated	
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated	
1	Housing	High Temp	Black	UL 94V-0	
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK	
TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.30	.X"±3"	PART NO. JXT-SATA04-A2-M22PX	TITLE: SATA 7+15P 母座 SMT H:5.00 板上型		
.XX±0.20	.XX"±2"				
.XXX±0.05	.XXX"±0.5"	DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm				
MATERILA	— — —	CHED: Olvia		SCALE	SHEET
FINISH	— — —	APPD: Ava		N:A	1/1