

RoHS

REV	ECN NO.	DESRPTION	DESIGN	APPROVAL	DATE
A1	NEW	新版发行			2026.07.21

SPECIFICATIONS

- Current rating: 1A AC, DC
- Temperature range: -25°C ~ +85°C
- Insulation resistance: 500MΩ Min.
- Withstanding voltage: 500V AC/ minute.
- Contact resistance: 20mΩ Max.







Material:
Insulator: LCP UL 94V-0
Contact: Brass
Plating: Plated Tin
Circuits: 02~16P
Mate with:XFCN P1510 series Housing

Ordering Code:
M1510VS-XXP-001
1 2

- 1.序列号
- 2.Pin位数 02-16P

No.of PIN/ROW	Dimension		
	A	B	C
2	6.00	3.60	1.50
3	7.50	5.10	3.00
4	9.00	6.60	4.50
5	10.50	8.10	6.00
6	12.00	9.60	7.50
7	13.50	11.10	9.00
8	15.00	12.60	10.50
9	16.50	14.10	12.00
10	18.00	15.60	13.50
11	19.50	17.10	15.00
12	21.00	18.60	16.50
13	22.50	20.10	18.00
14	24.00	21.60	19.50
15	25.50	23.10	21.00
16	27.00	24.60	22.50

X.±0.50	X.°±	PART NO: M1510VS-XXP-001		XFCN 兴飞连接器				
.X±0.25	.X°±							
.XX±0.15	.XX°±	TITLE: 1.50mm Crimp Style Connectors		0769-82001899				
.XXX±0.10	.XXX°±			www.xfconn.com				
UNITS:	mm	APPD Chen ZhiQiang		DWG NO: /				
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED.COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN				CHKD Liu Wei		VIEW		
				DRAW Chen HongJiang		SCALE	SHEET	REV
				DATE 2026.07.21		NONE	1/1	A1



RECOMMENDER P.C.B.LAYOUT TOP VIEW
(COMPONENT SIDE TOLERANCE±0.1)