


BN5A2V30

Schottky Barrier Diode

Features

- The plastic package carries UL Flammability Classification 94V-0
- For surface mounted applications
- Low power loss, high efficiency
- Built-in strain relief, ideal for automated placement
- High forward surge current capability
- High temperature soldering guaranteed: 260°C/10 seconds at terminals
- ESD Rating:
 - Human Body Model: Class 3B
 - Machine Model: Class C

Package



Applications

- Low voltage, high frequency inverters
- Freewheeling
- DC/DC converters
- Polarity protection application

Mechanical Data

- Package: DFN1610-2L
- UL Flammability Classification Rating 94V-0
- Packaging: Tape and Reel
- RoHS/WEEE Compliant

Marking



Ordering information

Order code	Package	Marking	Base qty	Delivery mode
BN5A2V30	DFN1610-2L	2A30	3K	Tape and reel



BN5A2V30

Schottky Barrier Diode

Maximum Ratings @ $T_A=25^{\circ}\text{C}$ unless otherwise noted

Symbol	Parameter	Value	Unit
V_{RRM}	Maximum repetitive peak reverse voltage	30	V
V_{RMS}	Maximum RMS voltage	21	V
I_{AV}	Maximum average forward rectified current	2	A
I_{FSM}	Peak Forward Surge Current (8.3ms single half sine wave or eq. square wave)	30	A
I^2t	I^2t Rating for Fusing ($t < 8.3\text{ms}$)	3.735	A ² s
$R_{\theta JA}$	Typical Thermal Resistance Junction to Ambient	500	$^{\circ}\text{C/W}$
T_J	Operating Temperature Range	-55 to +125	$^{\circ}\text{C}$
T_{STG}	Storage Temperature	-55 to +150	$^{\circ}\text{C}$

Electrical Characteristics @ $T_A=25^{\circ}\text{C}$ unless otherwise noted

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
V_{BR}	Breakdown Voltage	$I_{BR}=1\text{mA}$	45	—	—	V
V_F	Forward Voltage	$I_F=1\text{A}$	—	—	0.5	V
		$I_F=2\text{A}$	—	—	0.55	
I_R	Maximum DC reverse current	$V_R=30\text{V}, T_A=25^{\circ}\text{C}$	—	—	50	μA
		$V_R=30\text{V}, T_A=100^{\circ}\text{C}$	—	—	1000	
T_{rr}	Maximum reverse recovery time	$I_F = 10\text{mA}, I_R=10\text{mA}, R=100\Omega$	—	5	—	nS



BN5A2V30

Schottky Barrier Diode

Typical Performance Characteristics($T_J = 25^\circ\text{C}$, unless otherwise noted)

Figure 1: Forward Characteristics




Figure 2: Typical Reverse Characteristics




Figure 3: Typical Instantaneous Forward Characteristics






Figure 4: Maximum Non-Repetitive Peak Forward Surge Current



BN5A2V30

Schottky Barrier Diode

Outline Drawing - DFN1610-2L



SYMBOL	MILLIMETER		
	MIN.	Typ.	MAX.
A	0.45	0.50	0.55
A1	—	0.02	0.05
A2	0.119	0.127	0.135
E	1.55	1.60	1.65
D	0.95	1.00	1.05
b	—	0.80	—
e	1.1039BSC		
L	0.35	0.40	0.45
L1	0.05REF		

