

Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
60V	10.5m Ω @10V	12A
	14m Ω @4.5V	



合肥矽普半导体

Siliup Semiconductor Technology Co., Ltd

技术 品质 服务

www.siliup.com


Feature

- Fast Switching
- Advanced Split Gate Trench Technology
- **100% UIS TESTED**

Application


- Power Management
- Switched mode power supply

Package




SOP-8L

Circuit Diagram



Marking



Order Information

Device	Package	Unit/Tape
SP60N10GDP8	SOP-8L	4000

Absolute maximum ratings (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Rating	Unit
Drain-Source Voltage	V_{DSS}	60	V
Gate-Source Voltage	V_{GSS}	± 20	V
Continuous Drain Current (Ta=25°C)	I_D	12	A
Continuous Drain Current (Ta=100°C)	I_D	8	A
Pulse Drain Current Tested	I_{DM}	48	A
Single Pulse Avalanche Energy ¹	E_{AS}	100	mJ
Power Dissipation (Ta=25°C)	P_D	2	W
Power Dissipation (Ta=100°C)	P_D	0.8	W
Thermal Resistance Junction-to-Ambient	$R_{\theta JA}$	62.5	°C/W
Storage Temperature Range	T_J	-55 to 150	°C
Operating Junction Temperature Range	T_{STG}	-55 to 150	°C


Electrical characteristics (Ta=25°C, unless otherwise noted)

Characteristics	Symbol	Test Condition	Min	Typ	Max	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	VGS=0V , ID=250uA	60	-	-	V
Zero Gate Voltage Drain Current	IDSS	VDS=48V , VGS=0V	-	-	1	uA
Gate Leakage Current	IGSS	VGS=±20V , VDS=0V	-	-	±100	nA
Gate Threshold Voltage	VGS(th)	VDS=VGS , ID=250uA	1.0	1.6	2.5	V
Drain-Source On-state Resistance	RDS(ON)	VGS=10V , ID=6A	-	10.5	14	mΩ
		VGS=4.5V , ID=4A	-	14	19	
Gate Resistance	RG	f=1MHz	-	2.2	-	Ω
Dynamic Characteristics						
Input Capacitance	Ciss	VGS=0V , VDS=30V , f=1MHz	-	910	-	pF
Output Capacitance	Coss		-	220	-	
Reverse Transfer Capacitance	Crss		-	10	-	
Total Gate Charge	Qg	VDS=30V , VGS=10V , ID=10A	-	13	-	nC
Gate-Source Charge	Qgs		-	2.5	-	
Gate-Drain Charge	Qgd		-	3.2	-	
Gate Plateau Voltage	Vplateau		-	3	-	
Switching Characteristics						
Turn-On Delay Time	td(on)	VDD=30V , ID=10A , VGS=10V , RG=4.7Ω	-	14	-	nS
Rise Time	tr		-	26	-	
Turn-Off Delay Time	td(off)		-	33.8	-	
Fall Time	tf		-	26.4	-	
Drain-Source Body Diode Characteristics						
Source-Drain Diode Forward Voltage	VSD	VGS=0V , IS=1A , TJ=25℃	-	-	1.2	V
Maximum Body-Diode Continuous Current	IS		-	-	12	A
Reverse Recovery Time	Trr	IS=10A , di/dt=100A/μs , TJ=25℃	-	36	-	nS
Reverse Recovery Charge	Qrr		-	23	-	nC


Note :

1. The test condition is $V_{DD}=30V, V_{GS}=10V, L=0.5mH, R_G=25\Omega$;


Typical Characteristics




Output Characteristics




Transfer Characteristics




Capacitance Characteristics




Gate Charge




Current dissipation




Power dissipation




$R_{DS(on)}$ VS Drain Current




Forward characteristics of reverse diode




Normalized breakdown voltage



Normalized Threshold voltage





Safe Operation Area





Test Circuit



Gate Charge





Resistive Load Switching Time




Un-clamped Inductive Load Switching



Drain-Source Body Diode Reverse Recovery



Temperature Profile for IR Reflow Soldering



Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Preheat & Soak		
Temperature min (T _{smin})	100°C	150°C
Temperature max (T _{smax})	150°C	200°C
Time (T _{smin} to T _{smax}) (t _s)	60-120 seconds	60-120 seconds
Average ramp-up rate (T _{smax} to T _p)	3 °C/second max.	3°C/second max.
Liquidous temperature (T _L)	183 °C	217°C
Time at liquidous (t _L)	60-150 seconds	60-150 seconds
Peak package body Temperature e (T _p)*	See Classification Temp in table 1	See Classification Temp in table 2
Time (t _p)** within 5°C of the specified classification temperature (T _c)	20** seconds	30** seconds
Average ramp-down rate (T _p to T _{smax})	6 °C/second max.	6 °C/second max.
Time 25°C to peak temperature	6 minutes max.	8 minutes max.
* Tolerance for peak profile Temperature (T _p) is defined as a supplier minimum and a user maximum. ** Tolerance for time at peak profile temperature (t _p) is defined as a supplier minimum and a user maximum		


Table 1. SnPb Eutectic Process – Classification Temperatures (T_c)

Package Thickness	Volume mm ³ <350	Volume mm ³ ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2. Pb-free Process – Classification Temperatures (T_c)

Package Thickness	Volume mm ³ <350	Volume mm ³ 350-2000	Volume mm ³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 mm – 2.5 mm	260 °C	250 °C	245 °C
≥2.5 mm	250 °C	245 °C	245 °C


SOP8 Embossed Carrier Tape




Dimensions are in millimeter

Pkg type	a	B	c	d	E	F	P0	P	P1	W
SOP-8	6.40	5.40	2.10	Φ1.50	1.75	5.50	4.00	8.00	2.00	12.00

SOP8 Tape Leader and Trailer




SOP8 Reel



Dimensions are in millimeter

Reel Option	D	D1	D2	G	H	I	W1	W2
13"Dia	Ø330.00	100.00	13.00	R151.00	R56.00	R6.50	12.40	17.60

REEL	Reel Size	Box	Box Size(mm)	Carton	Carton Size(mm)	G.W.(kg)
4,000 pcs	13 inch	8,000 pcs	360×360×65	40,000 pcs	565×380×390	

SOP-8L Package Information


Symbol	Dimensions In Millimeters	
	Min.	Max.
A	1.35	1.75
A1	0.10	0.25
A2	1.35	1.55
b	0.33	0.51
c	0.17	0.25
D	4.80	5.00
e	1.27 REF.	
E	5.80	6.20
E1	3.80	4.00
L	0.40	1.27
θ	0°	8°