N-Ch and P-Ch Fast Switching MOSFETs

★Green Device Available
★Super Low Gate Charge
★Excellent CdV/dt effect decline★
Advanced high cell density Trench technology

Product Summary


Green


BVDSS	RDSON	ID
15V	8.7mΩ	12A
-15V	15.5mΩ	-12A

Description

The XR12G01S is the high performance complementary N-ch and P-ch MOSFETs with high cell density, which provide excellent RDSON and gate charge for most of the synchronous buck converter applications.
The XR12G01S meet the RoHS and Green

SOP8 Pin Configuration





Absolute Maximum Ratings

Symbol	Parameter	Rating		Units
		N-Ch	P-Ch	
V_{DS}	Drain-Source Voltage	15	-15	V
V_{GS}	Gate-Source Voltage	±12	±12	V
I_D@Ta=25℃	Continuous Drain Current, V_{GS} @ 10V[1]	12	-12	A
I_D@Ta=100℃	Continuous Drain Current, V_{GS} @ 10V[1]	6	-6	A
I_{DM}	Pulsed Drain Current[2]	40	-40	A
EAS	Single Pulse Avalanche Energy[3]	---	---	mJ
P_D@T_C=25℃	Total Power Dissipation[4]	1.8	1.6	W
T_{STG}	Storage Temperature Range	-55 to 150	-55 to 150	℃
T_J	Operating Junction Temperature Range	-55 to 150	-55 to 150	℃

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-Ambient [1]	---	115	℃/W
$R_{\theta JC}$	Thermal Resistance Junction-Case[1]	---	---	℃/W

N-Channel Electrical Characteristics (T_J=25℃ unless otherwise specified)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	V_{GS}=0V , I_D=250uA	15	---	---	V
$\triangle BV_{DSS}/\triangle T_J$	BVDSS Temperature Coefficient	Reference to 25℃ , I_D=1mA	---	---	---	V/℃
$R_{DS(ON)}$	Static Drain-Source On-Resistance[2]	V_{GS}=4.5V , I_D=1A	---	8.7	11	mΩ
		V_{GS}=2.5V , I_D=1A	---	11.5	15	
$V_{GS(th)}$	Gate Threshold Voltage	V_{GS}=V_{DS} , I_D =250uA	0.5	0.75	1.0	V
$\triangle V_{GS(th)}$	$V_{GS(th)}$ Temperature Coefficient		---	---	---	mV/℃
I_{DSS}	Drain-Source Leakage Current	V_{DS}=15V , V_{GS}=0V , T_J=25℃	---	---	1	uA
		V_{DS}=15V , V_{GS}=0V , T_J=55℃	---	---	---	
I_{GSS}	Gate-Source Leakage Current	V_{GS}=±12V , V_{DS}=0V	---	---	±100	nA
R_g	Gate Resistance	V_{DS}=0V , V_{GS}=0V , f=1MHz	---	---	---	Ω
Q_g	Total Gate Charge (4.5V)	V_{DS}=10 , V_{GS}=4.5V , I_D=4A	---	8	---	nC
Q_{gs}	Gate-Source Charge		---	1.8	---	
Q_{gd}	Gate-Drain Charge		---	2.1	---	
$T_{d(on)}$	Turn-On Delay Time	V_{DD}=10V , V_{GS}=4.5V , R_G=3Ω , I_D=4A	---	6	---	ns
T_r	Rise Time		---	23	---	
$T_{d(off)}$	Turn-Off Delay Time		---	27	---	
T_f	Fall Time		---	8	---	
C_{iss}	Input Capacitance	V_{DS}=10V , V_{GS}=0V , f=1MHz	---	570	---	pF
C_{oss}	Output Capacitance		---	102	---	
C_{rss}	Reverse Transfer Capacitance		---	63	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current[1,4]	V_G=V_D=0V , Force Current	---	---	12	A
V_{SD}	Diode Forward Voltage[2]	V_{GS}=0V , I_S=1A , T_J=25C	---	---	1.2	V
t_{rr}	Reverse Recovery Time	IF=4A ,di/dt=100A / μs , T_J= 2 5 C	---	---	---	nS
Q_{rr}	Reverse Recovery Charge		---	---	---	nC

Notes:1. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature

2. Pulse Test: Pulse Width≤300μs, Duty Cycle≤0.5%

P-Channel Electrical Characteristics (T_J=25℃ unless otherwise specified)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	V_{GS}=0V , I_D=-250uA	-15	---	---	V
$\Delta BV_{DSS}/\Delta T_J$	BV_{DSS} Temperature Coefficient	Reference to 25℃ , I_D=-1mA	---	---	---	V/℃
$R_{DS(ON)}$	Static Drain-Source On-Resistance[2]	V_{GS}=-4.5V , I_D=-1A	---	15.5	20.0	mΩ
		V_{GS}=-2.5V , I_D=-1A	---	21	27	
$V_{GS(th)}$	Gate Threshold Voltage	V_{GS}=V_{DS} , I_D =-250uA	-0.4	-0.7	-1	V
$\Delta V_{GS(th)}$	$V_{GS(th)}$ Temperature Coefficient		---	---	---	mV/℃
I_{DSS}	Drain-Source Leakage Current	V_{DS}=-15V , V_{GS}=0V , T_J=25℃	---	---	-1	uA
		V_{DS}=-15V, V_{GS}=0V , T_J=100℃	---	---	---	
I_{GSS}	Gate-Source Leakage Current	V_{GS}= ±12V , V_{DS}=0V	---	---	±100	nA
gfs	Forward Transconductance	V_{DS}=-5V , I_D=-20A	---	---	---	S
R_g	Gate Resistance	V_{DS}=0V , V_{GS}=0V , f=1MHz	---	---	---	Ω
Q_g	Total Gate Charge	V_{DS}=-10V , V_{GS}=-4.5V , I_D=-2A	---	8.8	---	nC
Q_{gs}	Gate-Source Charge		---	1.4	---	
Q_{gd}	Gate-Drain Charge		---	1.9	---	
$T_{d(on)}$	Turn-On Delay Time	V_{GS}=-4.5V, V_{DS}=-10V, I_D=-2A, R_{GEN}=10Ω	---	10	---	ns
T_r	Rise Time		---	32	---	
$T_{d(off)}$	Turn-Off Delay Time		---	50	---	
T_f	Fall Time		---	51	---	
C_{iss}	Input Capacitance	V_{DS}=-10V , V_{GS}=0V , f=1MHz	---	830	---	pF
C_{oss}	Output Capacitance		---	132	---	
C_{rss}	Reverse Transfer Capacitance		---	85	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current[1,5]	V_G=V_D=0V , Force Current	---	---	-12	A
V_{SD}	Diode Forward Voltage[2]	V_{GS}=0V , I_S=-13A , T_J=25℃	---	---	-1.2	V

Notes:1. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature

2. Pulse Test: Pulse Width≤300μs, Duty Cycle≤2%

Typical Performance Characteristics-N

Fig.1 Output Characteristics




Fig.2 Typical Transfer Characteristics




Fig.3 On-resistance VS Drain Current




Fig. 4 Body Diode Characteristics




Fig.5 Gate Charge Characteristics




Fig. 6 Capacitance Characteristics




Fig.7 Normalized Breakdown Voltage VS Junction Temperature




Fig. 8 Normalized On-Resistance Variation VS Junction Temperature




Fig.9 Maximum Continuous Drain Current VS. Case Temperature




Fig.10 Maximum Safe Operating Area





Fig. 11 Maximum Effective Transient Thermal Impedance，Junction-to-Ambient



Typical Performance Characteristics

Figure1: Output Characteristics




Figure 2: Typical Transfer Characteristics




Figure 3: On-resistance vs. Drain Current




Figure 4: Body Diode Characteristics




Figure 5: Gate Charge Characteristics




Figure 6: Capacitance Characteristics




Figure 7: Normalized Breakdown Voltage vs. Junction Temperature




Figure 8: Normalized on Resistance vs. Junction Temperature




Figure 9: Maximum Safe Operating Area




Figure 10: Maximum Continuous Drain Current vs. Ambient Temperature






Figure.11: Maximum Effective Transient Thermal Impedance, Junction-to-Ambient



SOP-8 Package Information



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	1.350	1.750	0.053	0.069
A1	0.100	0.250	0.004	0.010
A2	1.350	1.550	0.053	0.061
b	0.330	0.510	0.013	0.020
c	0.170	0.250	0.006	0.010
D	4.700	5.100	0.185	0.200
E	3.800	4.000	0.150	0.157
E1	5.800	6.200	0.228	0.244
e	1.270(BSC)		0.050(BSC)	
L	0.400	1.270	0.016	0.050
θ	0°	8°	0°	8°