

Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
100V	3.9mΩ@10V	130A



合肥矽普半导体

Siliup Semiconductor Technology Co., Ltd

技术 品质 服务

www.siliup.com


Feature

- Fast Switching
- Low Gate Charge and Rdson
- Advanced Split Gate Trench Technology
- **100% UIS TESTED**

Applications


- Power switching application
- DC-DC Converter
- Power Management

Package




TO-263(1:G 2:D 3:S)

Circuit diagram



Marking



Order Information

Device	Package	Unit/Tape
SP010N04AGHTD	TO-263	800

Absolute maximum ratings (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Rating	Unit
Drain-Source Voltage	V_{DS}	100	V
Gate-Source Voltage	V_{GS}	± 20	V
Continuous Drain Current (Tc=25°C)	I_D	130	A
Continuous Drain Current (Tc=100°C)	I_D	87	A
Pulsed Drain Current	I_{DM}	520	A
Single Pulse Avalanche Energy ¹	E_{AS}	841	mJ
Power Dissipation (Tc=25°C)	P_D	180	W
Power Dissipation (Tc=100°C)	P_D	72	W
Thermal Resistance Junction-to-Case	$R_{\theta JC}$	0.69	°C/W
Storage Temperature Range	T_{STG}	-55 to 150	°C
Operating Junction Temperature Range	T_J	-55 to 150	°C


Electrical characteristics (Ta=25°C, unless otherwise noted)

Characteristics	Symbol	Test Condition	Min	Typ	Max	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	VGS=0V , ID=250uA	100	-	-	V
Drain Cut-Off Current	IDSS	VDS=80V , VGS=0V , TJ=25℃	-	-	1	uA
Gate Leakage Current	IGSS	VGS=±20V , VDS=0V	-	-	±100	nA
Gate Threshold Voltage	VGS(th)	VGS=VDS , ID =250uA	2.6	3.0	3.4	V
Drain-Source ON Resistance	RDS(ON)	VGS=10V , ID=30A	-	3.9	5.2	mΩ
Gate Resistance	RG	f=1MHz	-	2.8	-	Ω
Dynamic Characteristics						
Input Capacitance	Ciss	VDS=50V , VGS=0V , f=1.0MHz	-	4251	-	pF
Output Capacitance	Coss		-	692	-	
Reverse Transfer Capacitance	Crss		-	26	-	
Total Gate Charge	Qg	VDS=50V , VGS=10V , ID=20A	-	69	-	nC
Gate-Source Charge	Qgs		-	24	-	
Gate-Drain Charge	Qgd		-	18	-	
Gate Plateau Voltage	Vplateau		-	5.6	-	V
Switching Characteristics						
Turn-On Delay Time	td(on)	VGS=10V , VDS=50V , RL=2.5Ω , RG=3.0Ω	-	12	-	nS
Rise Time	tr		-	23	-	
Turn-Off Delay Time	td(off)		-	37	-	
Fall Time	tr		-	16	-	
Drain-Source Body Diode Characteristics						
Source-Drain Diode Forward Voltage	VSD	VGS=0V , IS=1A , TJ=25℃	-	-	1.2	V
Maximum Body-Diode Continuous Current	Is		-	-	130	A
Reverse Recovery Time	Trr	IS=20A, di/dt=100A/us, TJ=25℃	-	65	-	nS
Reverse Recovery Charge	Qrr		-	126	-	nC


Note:

- The test condition is $V_{DD}=50V, V_{GS}=10V, L=0.5mH, R_G=25\Omega$;


Typical Characteristics




Typical Output Characteristics




Transfer Characteristics




On-Resistance vs. Drain Current




On-Resistance vs. Junction Temperature




Body-Diode Characteristics




Capacitance Characteristics




Current De-rating




Power De-rating



Maximum Safe Operating Area





Single Pulse Power Rating, Junction-to-Case





Normalized Maximum Transient Thermal Impedance

Test Circuit



Gate Charge





Resistive Load Switching Time




Un-clamped Inductive Load Switching



Drain-Source Body Diode Reverse Recovery



Temperature Profile for IR Reflow Soldering



Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Preheat & Soak		
Temperature min (T _{min})	100°C	150°C
Temperature max (T _{max})	150°C	200°C
Time (T _{min} to T _{max}) (t _s)	60-120 seconds	60-120 seconds
Average ramp-up rate (T _{max} to T _p)	3 °C/second max.	3°C/second max.
Liquidous temperature (T _L)	183 °C	217°C
Time at liquidous (t _L)	60-150 seconds	60-150 seconds
Peak package body Temperature e (T _p)*	See Classification Temp in table 1	See Classification Temp in table 2
Time (t _p)** within 5°C of the specified classification temperature (T _c)	20** seconds	30** seconds
Average ramp-down rate (T _p to T _{max})	6 °C/second max.	6 °C/second max.
Time 25°C to peak temperature	6 minutes max.	8 minutes max.
* Tolerance for peak profile Temperature (T _p) is defined as a supplier minimum and a user maximum. ** Tolerance for time at peak profile temperature (t _p) is defined as a supplier minimum and a user maximum		


Table 1. SnPb Eutectic Process – Classification Temperatures (T_c)

Package Thickness	Volume mm ³ <350	Volume mm ³ ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2. Pb-free Process – Classification Temperatures (T_c)

Package Thickness	Volume mm ³ <350	Volume mm ³ 350-2000	Volume mm ³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 mm – 2.5 mm	260 °C	250 °C	245 °C
≥2.5 mm	250 °C	245 °C	245 °C

TO-263 Reel Information




Packaging Description:

TO-263 parts are shipped in tape. The carrier tape is made from a dissipative (carbon filled) polycarbonate resin. The cover tape is a multilayer film (Hear Activated Adhesive in nature) primarily composed of polyester film, adhesive layer, sealant, and anti-static sprayed agent. These reeled parts in standard option are shipped with 800 units per 13" or 33.0 cm diameter reel. The reels are clear in color and is made of polystyrene plastic (anti-static coated).


Dimensions are in millimeter

Pkg type	A	B	C	d	E	F	P0	P	P1	W
TO-263	10.80	16.13	5.21	Φ1.55	1.75	11.50	4.00	16.00	2.00	24.00

TO-263 Tape Leader and Trailer



TO-263 Reel




Dimensions are in millimeter

Reel	D	D1	D2	W1	W2	I
13" Dia	330.00	100.00	Φ21.00	24.40	30.40	Φ13.00

Reel	Reel Size	Box	Box Size(mm)	Carton	Carton Size(mm)
800 pcs	13 inch	1600 pcs	360×360×65	8000 pcs	378×358×382

TO-263 Package Information



Symbol	Dimensions In Millimeters	
	Min.	Max.
A	4.40	4.67
A1	0.02	0.23
b	0.70	0.90
b1	1.21	1.40
c	0.40	0.60
c1	1.25	1.45
D	9.00	9.30
D1	8.10 REF	
E	9.70	10.20
E1	7.00	8.20
e	2.54 TYP.	
H	14.80	15.40
L1	1.10	1.40
L2	1.10	1.70
L3	2.10	2.50
θ	0°	9°