


Rev No.	Description of Revision	Date	Name	Approved	ECN No.
A					









RECOMMENDED PCB LAYOUT


GENERAY TOLERANCE ±0.05






NOTES:


1. ELECTRICAL CHARACTERISTICS
   - 1-1. CONTACT RESISTANCE: 60 Milliohms Max
   - 1-2. INSULATION RESISTANCE: 1,000 Megohms Min.
   - 1-3. DIELECTRIC WITHSTANDING VOLTAGE: 500V AC FOR 1 MINUTE.
2. MECHANICAL CHARACTERISTICS
   - 2-1. OPERATION TEMPERATURE RANGE: -25°C~+70°C
   - 2-2. DURABILITY: 5000 CYCLES
3. MATERIAL:
   - 3-1. HOUSING: THERMOPLASTIC,UL 94-V0
   - 3-2. TERMINAL: PHOSPHOR BRONZE,T=0.15
   - 3-3. SHELL: STAINLESS STEEL,T=0.15
4. FINISHED:
   - 4-1. TERMINAL: Ni PLATED UNDER,Au PLATED ON CONTACT AREA,G/F PLATED ON SOLDERTAIL
   - 4-2. SHELL: Ni PLATED UNDER,G/F PLATED ON SOLDERTAIL



STEP 1 INSERT Micro-SIM CARD



STEP 2 PUSH THE SHELL





STEP 3 FINISH


SIM CARD	
Pin No.	NAME
C1	VCC
C2	RST
C3	CLK
C4	RESERVED
C5	GND
C6	VPP
C7	I/O
C8	RESERVED


UNLESS OTHERWSE SPECIFED TOLERANCES		广东国连电子有限公司 GUANGDONG GUOLIAN ELECTRONICS CO.,LTD			
DECIMALS:	ANGLES	TITLE: 掀盖MICRO SIM CARD 8PIN 1.5H			
X. ±0.20	X° ±2°	Drdwn. JACK.LI	PART NO. MIB5FS1082E5		
X.X ±0.15	X.X° ±1°	Checked. PETER.LIU	SCALE. 1:1	UNIT. mm	PROJ.
X.XX ±0.10	X.XX° ±0.5°	Approved. JACK.D	SIZE. A4	SHEET. 1 OF 1	REV. A
X.XXX ±0.05		CUSTOMER COPY			

Rev No.	Description of Revision	Date	Name	Approved	ECN No.
A					









NOTES:

1. 10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE±0.2.
2. CARRIER CAMBER IS WITHIN 1 MM IN 250MM.
3. MATERIAL: CLARITY CONDUCTIVE POLYSTYRENE ALLOY
   100% RECYCLABLE.
4. ALL DIMENSIONS MEET EIA-481-3 REQUIREMENTS.
5. THICKNESS: 0.30±0.05MM
6. COMPONENT LOAD PER 13" REEL: 1000PCS.
7. 10REEL/CARTON: 10000PCS

UNLESS OTHERWSE SPECIFED TOLERANCES		广东国连电子有限公司 GUANGDONG GUOLIAN ELECTRONICS CO.,LTD			
DECIMALS:	ANGLES	TITLE: 掀盖MICRO SIM CARD 8PIN 1.5H			
X. ±0.20	X° ±2°	Drdwn. JACK.LI	PART NO. MIB5FS1082E5		
X.X ±0.15	X.X° ±1°	Checked. PETER.LIU	SCALE. 1:1	UNIT. mm	PROJ.
X.XX ±0.10	X.XX° ±0.5°	Approved. JACK.D	SIZE. A4	SHEET. 1 OF 1	REV. A
X.XXX ±0.05		CUSTOMER COPY			