

Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
120V	1.7mΩ@10V	345A



合肥矽普半导体

Siliup Semiconductor Technology Co., Ltd

技术 品质 服务

www.siliup.com


Feature

- Fast Switching
- Low Gate Charge and Rdson
- Low Reverse transfer capacitances
- **100% UIS TESTED**
- **100% ΔVds TESTED**

Applications


- High Speed Power switching
- DC-DC Converter
- Power Management

Package



TOLL-8L

Circuit diagram



Marking



SP012N02AAGHTO :Device Code
** :Week Code

Order Information

Device	Package	Unit/Tube
SP012N02AAGHTO	TOLL-8L	2000

Absolute maximum ratings (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Rating	Units
Drain-Source Voltage	V_{DS}	120	V
Gate-Source Voltage	V_{GS}	± 20	V
Continuous Drain Current (Tc=25°C)	I_D	345	A
Continuous Drain Current (Tc=100°C)	I_D	230	A
Pulsed Drain Current	I_{DM}	1380	A
Single Pulse Avalanche Energy ¹	E_{AS}	2916	mJ
Power Dissipation (Tc=25°C)	P_D	360	W
Power Dissipation (Tc=100°C)	P_D	144	W
Thermal Resistance Junction-to-Case	$R_{\theta JC}$	0.35	°C/W
Storage Temperature Range	T_{STG}	-55 to 150	°C
Operating Junction Temperature Range	T_J	-55 to 150	°C


Electrical characteristics (Ta=25°C, unless otherwise noted)

Characteristics	Symbol	Test Condition	Min	Typ	Max	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	ID=250μA , VGS=0V	120	135	-	V
Drain Cut-Off Current	IDSS	VDS=96V , VGS=0V	-	-	1	μA
Gate Leakage Current	IGSS	VGS=±20V , VDS=0V	-	-	±100	nA
Gate Threshold Voltage	VGS(th)	VDS=VGS , ID=250μA	2.6	3.2	3.6	V
Drain-Source ON Resistance	RDS(ON)	VGS=10V , ID=50A	-	1.7	2.25	mΩ
Gate Resistance	RG	f=1MHz	-	2.16	-	Ω
Dynamic Characteristics						
Input Capacitance	Ciss	VDS=60V , VGS=0V , f=1.0MHz	-	10852	-	pF
Output Capacitance	Coss		-	1352	-	
Reverse Transfer Capacitance	Crss		-	49	-	
Total Gate Charge	Qg	VDS=60V , VGS=10V , ID=100A	-	200	-	nC
Gate-Source Charge	Qgs		-	56	-	
Gate-Drain Charge	Qgd		-	52	-	
Gate Plateau Voltage	Vplateau		-	5	-	V
Switching Characteristics						
Turn-On Delay Time	td(on)	VDS=60V , VGS=10V , ID=100A , RG=1.6Ω	-	32	-	nS
Rise Time	tr		-	25	-	
Turn-Off Delay Time	td(off)		-	72	-	
Fall Time	tf		-	27	-	
Drain-Source Body Diode Characteristics						
Source-Drain Diode Forward Voltage	VSD	IS=1A , VGS=0V , TJ=25℃	-	-	1.2	V
Maximum Body-Diode Continuous Current	IS		-	-	345	A
Reverse Recovery Time	Trr	IS=100A , di/dt=100A/us , TJ=25℃	-	103	-	nS
Reverse Recovery Charge	Qrr		-	264	-	nC


Note :

1. The test condition is $V_{DD}=60V$, $V_{GS}=10V$, $L=0.5mH$, $R_G=25\Omega$;


Typical Characteristics




Output Characteristics




Transfer Characteristics




Capacitance Characteristics




Gate Charge




Current dissipation




Power dissipation




$R_{DS(on)}$ vs. Drain Current




Forward characteristics of reverse diode




Normalized breakdown voltage



Normalized Threshold voltage





Safe Operation Area





Test Circuit



Gate Charge





Resistive Load Switching Time




Un-clamped Inductive Load Switching



Drain-Source Body Diode Reverse Recovery



Temperature Profile for IR Reflow Soldering



Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Preheat & Soak		
Temperature min (T _{Smin})	100°C	150°C
Temperature max (T _{Smax})	150°C	200°C
Time (T _{Smin} to T _{Smax}) (t _s)	60-120 seconds	60-120 seconds
Average ramp-up rate (T _{Smax} to T _P)	3 °C/second max.	3°C/second max.
Liquidous temperature (T _L)	183 °C	217°C
Time at liquidous (t _L)	60-150 seconds	60-150 seconds
Peak package body Temperature e (T _P)*	See Classification Temp in table 1	See Classification Temp in table 2
Time (t _p)** within 5°C of the specified classification temperature (T _C)	20** seconds	30** seconds
Average ramp-down rate (T _P to T _{Smax})	6 °C/second max.	6 °C/second max.
Time 25°C to peak temperature	6 minutes max.	8 minutes max.
* Tolerance for peak profile Temperature (T _P) is defined as a supplier minimum and a user maximum. ** Tolerance for time at peak profile temperature (t _p) is defined as a supplier minimum and a user maximum		

Table 1. SnPb Eutectic Process – Classification Temperatures (T_C)



Package Thickness	Volume mm ³ <350	Volume mm ³ ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2. Pb-free Process – Classification Temperatures (T_C)


Package Thickness	Volume mm ³ <350	Volume mm ³ 350-2000	Volume mm ³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 mm – 2.5 mm	260 °C	250 °C	245 °C
≥2.5 mm	250 °C	245 °C	245 °C

TOLL-8L Reel Information

REEL DIMENSIONS




TAPE DIMENSIONS



- A0: Dimension designed to accommodate the component width
- B0: Dimension designed to accommodate the component length
- K0: Dimension designed to accommodate the component thickness
- W: Overall width of the carrier tape
- P0: Pitch between successive cavity centers and sprocket hole
- P1: Pitch between successive cavity centers
- P2: Pitch between sprocket hole
- T: Tape material thickness
- D1: Reel Diameter
- W1: Reel Width

DIMENSIONS										(Unit: mm)
Reel	D1	W1								Material
	330	24.4								Hips
Tape	P0	P1	P2	W	A0	B0	K0	T	Pin 1 Quadrant	Material
	2	4	12	24	10.3	12.1	2.6	0.35	Q1	PC

All dimensions are nominal

TOLL-8L Package Information


Symbol	Dimensions In Millimeters		
	Min.	Nom.	Max.
A	2.15	2.30	2.45
b	0.60	0.75	0.90
C	0.40	0.50	0.60
D	10.18	10.38	10.58
D1	3.15	3.3	3.45
E	9.70	9.90	10.10
E1	9.65	9.80	9.95
E2	7.90	--	9.15
E3	7.20	--	8.40
e	1.20 BSC		
F	1.05	1.20	1.35
H	11.45	11.70	11.95
H2	6.75	7.00	7.3
H3	3.00 BSC		
L	1.20	--	2.10
L1	0.50	0.75	0.90
L2	0.45	0.6	0.75
M	0.08 REF.		
β	8°	10°	12°