



客户图

NO.	ECN NO.	DESCRIPTION	DATE









RECOMMENDED PCB LAYOUT

Note:

1: Material(材料）:
Housing: PA9T(胶芯:PA9T)
Barrel: Brass C3604 （针管：黄铜 C3604）
Plunger: Brass C3604 （针管：黄铜 C3604）
Spring: SUS304 （弹簧：SUS304）
Magnet: NdFeB （磁铁：钕铁硼）

2: Plating(电镀）:
Barrel: 3u' Au over 80u'~120u' Ni over 80u'~120u' Cu(针管：镀金3u'，镍底80u'~120u'，铜底80u'~120u'。）
Plunger: 3u' Au over 80u'~120u' Ni over 80u'~120u' Cu(针管：镀金3u'，镍底80u'~120u'，铜底80u'~120u'。）
Magnet : Nickel plating (镀镍)
Spring: Gold plated (弹簧：镀金)

3: Electrical(电气特性）:
Rated Current & Voltage: DC 12V;1A（额定电压&电流：直流12V,1A）
Contact Resistance: 50 mohm Max. at working height.
接触电阻：最大50毫欧（在工作高度状态下）
Insulation Resistance: 1,000MΩ minimum. （绝缘电阻：1,000MΩ以上）
Dielectric Withstand Voltage: 500VAC/minute. （抗击电压：500VAC/minute）

4: Mechanical(机械性能）:
Force: 30g±20% at working height. (30g±20% 在工作高度）。
Durability: 10.000 cycles(min)（寿命：10000次）

5: WorkTemperature(工作环境)：
Withstanding Higt Temperature: 280℃
Operational Temperature: －20℃~ ＋70℃

深圳市鑫探技术有限公司
HTTP://WWW.XYZPOGOPIN.COM
TEL:0755-28773277 FAX:0755-28891353

SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2026.9.9	VER.	A.1

THE UNMARKED TOLERANCE ARE AS BELOW :

LENGTH		ANGLE	
X.XX	±0.05mm	X.XX	±0.50°
X.X	±0.10mm	X.X	±1.00°
X.	±0.20mm	X.	±2.00°

DESIGNED BY:		DWG. NO.	YZCP0644-20073-03025-01
CHECKED BY:		TITLE:	Pogo pin 连接器
APPROVED BY:			