

BKZ120N75HZ1

1200V 75A Trench FS IGBT

Description

The BKZ120N75HZ1 is a Trench FS IGBT utilizing bestirpower's advanced technology, which achieves an exceptionally low gate charge. It achieves significantly higher efficiency through optimized gate charge management, while its user-friendly design offers designers advantages such as low EMI and reduced switching losses.


V_{CE}	I_C ($T_C = 100^\circ\text{C}$)	V_{CEsat}	$Q_{g,typ}$
1200 V	75 A	1.95 V	307 nC

Applications

- Resonant converters
- Uninterruptible power supplies
- Welding converters

Features

- Maximum junction temperature $T_{Jmax} = 175^\circ\text{C}$
- Low saturation voltage $V_{CEsat} = 1.95\text{ V}$ at $T_J = 25^\circ\text{C}$
 V_{CEsat} is a positive temperature coefficient, suitable for parallel applications



Absolute Maximum Ratings

Symbol	Parameter		Value max	Unit	Note
V_{CE}	Collector-emitter voltage ($T_J \geq 25^\circ\text{C}$)		1200	V	
V_{GE}	Gate-emitter voltage		± 20	V	
I_C	DC collector current, limited by T_{Jmax}	$T_C = 25^\circ\text{C}$	110	A	
		$T_C = 100^\circ\text{C}$	75	A	
$I_{C,pulse}$	Pulsed collector current, t_p limited by T_{Jmax}		240	A	
I_F	Diode forward current, limited by T_{Jmax}	$T_C = 25^\circ\text{C}$	78	A	
		$T_C = 100^\circ\text{C}$	55	A	
$I_{F,pulse}$	Diode pulsed current, t_p limited by T_{Jmax}		180	A	
P_{tot}	Power Dissipation	$T_C = 25^\circ\text{C}$	536	W	Fig.8
		$T_C = 100^\circ\text{C}$	268		
T_J	Junction temperature range		-40 ~ 175	$^\circ\text{C}$	
T_{STG}	Storage temperature range		-55 ~ 150	$^\circ\text{C}$	

Thermal Resistance

Symbol	Parameter	Value	Unit
R_{thJC}	IGBT thermal resistance, junction-case	0.28	$^\circ\text{C/W}$
R_{thJC}	Diode thermal resistance, junction-case	0.48	$^\circ\text{C/W}$
R_{thJA}	Thermal resistance, junction-to-ambient	25.25	$^\circ\text{C/W}$
T_{sold}	Soldering temperature, wave soldering only allowed at leads	260	$^\circ\text{C}$

Electrical Characteristics ($T_J = 25^\circ\text{C}$ unless otherwise)

Symbol	Parameter	Test Conditions		Min	Typ	Max	Unit	Note
Statistic Characteristics								
V _{(BR)CES}	Collector-emitter Breakdown Voltage	V _{GE} =0V, I _C =1mA		1200	-	-	V	
I _{CES}	Collector Cut-off Current	V _{CE} =1200V, V _{GE} =0V		-		50	μA	
I _{GES}	Gate-emitter Leakage Current	V _{GE} =±20V, V _{CE} =0V		-	-	±100	nA	
V _{GE(TH)}	Gate Threshold Voltage	V _{CE} =V _{GE} , I _C =1.5mA		5.0	5.9	6.5	V	Fig.5
V _{CE(sat)}	Collector-Emitter Saturation Voltage	V _{GE} =15V I _C =75A	T _J =25°C	-	1.95	3.0	V	Fig.4
			T _J =150°C	-	3.0	-		
t _{sc}	Short circuit withstand time	V _{CC} =600V,V _{GE} =15V,T _J =25°C			11		μs	
Dynamic Characteristics								
C _{ies}	Input Capacitance	V _{CE} =25V, V _{GE} =0V, f=1MHz		-	7190	-	pF	Fig.6
C _{oes}	Output Capacitance			-	248	-		
C _{res}	Reverse Transfer Capacitance			-	20.9	-		
Switching Parameters								
t _{d(on)}	Turn-on Delay Time	V _{CE} =600V, I _C =75A, R _G =10Ω, V _{GE} =0/+15V	T _J =25°C	-	101	-	ns	Fig.17
			T _J =150°C	-	105	-	ns	
t _r	Rise Time		T _J =25°C	-	57	-	ns	Fig.17
			T _J =150°C	-	63.7	-	ns	
t _{d(off)}	Turn-off Delay Time		T _J =25°C	-	391.8	-	ns	Fig.17
			T _J =150°C	-	429	-	ns	
t _f	Fall Time		T _J =25°C	-	198	-	ns	Fig.17
			T _J =150°C	-	234	-	ns	
E _{on}	Turn-on Switching Energy		T _J =25°C	-	3342	-	uJ	Fig.18
			T _J =150°C	-	4965	-	uJ	
E _{off}	Turn-off Switching Energy		T _J =25°C	-	5920	-	uJ	Fig.18
			T _J =150°C	-	7455	-	uJ	
T _{rr}	Diode Reverse Recovery Time	V _R =600V, I _F =75A, di/dt=1086A/μs		-	293	-	ns	
Q _{rr}	Diode Reverse Recovery Charge			-	4.2	-	nC	
I _{rrm}	Diode Peak Reverse Recovery Current			-	34	-	A	
V _F	Diode forward voltage	I _F =75A,T _J =25°C		-	2.3	-	V	

Gate Charge Characteristics

Q _g	Gate Charge Total	V _{CE} =960V, I _C =75A V _{GE} =0 to 15V	-	307	-	nC	Fig.7
Q _{gc}	Gate-emitter charge		-	105	-		
Q _{ge}	Gate-collector charge		-	120	-		

Typical Performance Characteristics

Fig 1. Typical output characteristics




Fig 2. Typical Output characteristics




Fig 3. Typical transfer characteristic





Fig 4. Typical collector-emitter saturation voltage as a function of junction temperature



Typical Performance Characteristics

Figure 5. Gate-emitter threshold voltage as a function of junction temperature




Figure 6. Typical capacitance as a function of collector-emitter voltage




Figure 7. Typical gate charge





Figure 8. Power dissipation as a function of case temperature



Typical Performance Characteristics

Figure 9. IGBT transient thermal impedance as a function of pulse width




Figure 10. Diode transient thermal impedance as a function of pulse width




Figure 11. Typical Turn-on times as a function of collector current





Figure 12. Typical switching times as a function of collector emitter voltage



Typical Performance Characteristics

Figure 13. Typical switching times as a function of gate resistor




Figure 14. Typical switching energy losses as a function of collector current




Figure 15. Typical switching energy losses as a function of collector emitter voltage





Figure 16. Typical switching energy losses as a function of gate resistor



Typical Performance Characteristics

Figure 17. Typical switching times as a function of junction temperature




Figure 18. Typical switching energy losses as a function of junction temperature




Figure 19. Typical diode forward current as a function of forward voltage





Figure 20. Reverse bias safe operating area



Typical Performance Characteristics

Figure 21. Switching time test circuit and waveforms








Figure 22. Reverse recovery time test circuit and waveforms



Package Outlines

TO247-4L



SYMBOL	NM		
	MIN	NOM	MAX
A	4.80	5.00	5.20
A1	2.21	2.41	2.61
A2	1.80	2.00	2.20
b	1.06	1.21	1.36
b1	2.33	2.63	2.93
b3	1.07	1.30	1.60
c	0.51	0.61	0.75
D	23.30	23.45	23.60
D1	16.25	16.55	16.85
E	15.74	15.94	16.14
E1	13.72	14.02	14.32
T1	2.35	2.50	2.65
e	2.54 BSC		
e1	5.08 BSC		
Q	5.49	5.79	6.09
L	17.27	17.57	17.87
L1	3.99	4.19	4.39
Φp	3.40	3.60	3.80
Φp1	7.19 REF		

* Dimensions in millimeters

Package Marking and Ordering Information

Part Number	Top Marking	Package	Packing Method	Quantity
BKZ120N75HZ1	BKZ120N75HZ1	TO247-4L	Tube	50 units

Disclaimer

Bestirpower reserve the right to make changes, corrections, enhancements, modifications, and improvements to Bestirpower products and/or to this document at any time without notice.

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. Bestirpower does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Products or technical information described in this document.

This document is the property of Bestirpower Co., LTD., and not allowed to copy or transformed to other format if not under the authority approval.

© 2026 bestirpower – All rights Reserved