



RoHS

REV.	EC#	DESCRIPTION	DATE	DRAWING	CHECKED	APPROVED
A0	————	版新版发行	2020.09.17	MO	TEDDY	SUNNLY











RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ±0.05

PAD
KEEP OUT AREA






NANO SIM CARD

NOTES:

1)MATERIAL:
HOUSING:HI-TEMP. PLASIC UL 94V-0
CONTACT:COPPER ALLOY
SHELL:STANLESS STEEL
2). PLATING :
TERMINAL:
CONTACT AREA: Au GOLD FLASH.
SOLDER AREA: AU GOLD FLASH.
UNDER PLATE: NICKEL.
SHELL: NICKEL PLATED OVER ALL.
SOLDER AREA: GOLD FLASH.
3. SPECIALITY:
3.1 Rated current:1.0A
3.2 Rated voltage:30V
3.3 Contact Resistance:100mΩ MAX
3.4 Insulation Resistance:1000MΩ MIN 500V DC
3.5 Dielectric withstanding voltage: 500V AC.
3.6 Solder ability:260+0/-5℃, 30±10s.
3.7 Durability:5000 Cycles Min.
3.8 Operating condition:Temperature-40℃~+85℃;
Humidity 80% R.H MAX

CRICUIT DIAGRAM FOR CARD DETECT SWITCH



SIM pin Assignment	
PIN#	Name
C1	VCC
C2	RST
C3	CLK
C5	GND
C6	VPP
C7	I/O

MILLIMETERS	INCH
X.° ± 2°	X.° ± 2°
.X ±0.30	.XX ±0.012
.XX ±0.20	.XXX ±0.008
.XXX± 0.10	.XXXX± 0.004


UNITS	MM
MAT'L	SEE NOTES
FINISH	SEE NOTES
QTY	SEE NOTES


广东国连电子有限公司
GUANGDONG GUOLIAN ELECTRONICS CO.,LTD

PART NUMBER:	NNB5FW1072F1
TITLE:	NANO 自弹 SIM卡 1.37H(新版)
APPD:	
DWG NO.:	
CHKD:	
DR:	

SCALE	SHEET	REV.
1:1	1/2	A0


RoHS







NOTES

1. 每卷包装数量:1500PCS/每卷
2. 卷带包装方式:




3. 每箱包装数量:15000PCS/箱
4. 纸箱350mm*350mm*340mm(内部尺寸),材质K=K





将10卷产品放入箱内



MILLIMETERS	INCH
X.° ± 2°	X.° ± 2°
.X ±0.30	.XX ±0.012
.XX ±0.20	.XXX ±0.008
.XXX±0.10	.XXXX± 0.004

UNITS	MM
MAT'L	SEE NOTES
FINISH	SEE NOTES
QTY	SEE NOTES

广东国连电子有限公司
GUANGDONG GUOLIAN ELECTRONICS CO.,LTD

PART NUMBER: C-NNB5FW1072F1	TITLE: NANO 自弹 SIM卡 1.37H(新版)
APPD:	DWG NO.:
CHKD:	
DR:	

SCALE	SHEET	REV.
1:1	2/2	A0